

QO250CP

Mini circuit breaker, QO, 50A, 2 pole,
120/240VAC, 10kA, plug in mount, consumer
pack



Main

Product	Miniature circuit-breaker
Range	QO
Current Rating	50 A
Voltage Rating	120/240 V AC 120 V AC
Mounting Type	Plug-in
Number of Poles	2P
Circuit Breaker Type	Standard
Ratings	HACR rated
Electrical Connection	Box lugs
Type of Packing	Consumer packaging

Complementary

Interrupt Rating	10 KA 120/240 V AC 50/60 Hz 10 kA 120 V AC 50/60 Hz
Number of Panel Spaces	2
Wire Size	AWG 8...AWG 2 copper or aluminium
Tightening Torque	44.25 lbf.in (5 N.m) 0.02...0.04 in ² (10...25 mm ²) (AWG 8...AWG 2)
Height	3.11 in (79 mm)
Width	1.50 in (38 mm)
Depth	2.91 in (74 mm)
Net Weight	0.60 lb(US) (0.272 kg)

Environment

Certifications	UL Listed CSA
Ambient Rating	104 °F (40 °C)

Ordering and shipping details

Category	01341-QO 2 POLE BULK BRKRS15-60A
Discount Schedule	CPQ
GTIN	047569838057
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.50 in (3.81 cm)
Package 1 Width	3.20 in (8.128 cm)
Package 1 Length	3.10 in (7.874 cm)
Package 1 Weight	9.60 oz (272.155 g)
Unit Type of Package 2	PAL
Number of Units in Package 2	1800
Package 2 Height	40.00 in (101.6 cm)

Package 2 Width	40.00 in (101.6 cm)
Package 2 Length	48.00 in (121.92 cm)
Package 2 Weight	1095.00 lb(US) (496.683 kg)
Unit Type of Package 3	BB1
Number of Units in Package 3	5
Package 3 Height	3.20 in (8.128 cm)
Package 3 Width	3.20 in (8.128 cm)
Package 3 Length	7.70 in (19.558 cm)
Package 3 Weight	3.00 lb(US) (1.361 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Halogen content performance	Halogen free product