

JOVE

F7536-PBR

Soft and sculptural, the Jove family filters light through an organic, jewelry-like lens. Each cloud seedy glass shade hangs from a looping Patina Brass frame, recalling the drape of a necklace. The cords can be adjusted to varying lengths, allowing for a customized composition. Available as a 1-light sconce, 1-light pendant, or 3-chandelier and 4-light linear, Jove is both a highly usable fixture and a statement-making ornament.

FINISHES

PATINA BRASS

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 18.5"

Width/Diameter: 36.5"

Minimum Height: 22"

Maximum Height: 140"

Canopy/Backplate: 11.75"

Hanging Type: 144" Braided Cord

Product Weight: 14lb

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: No

Shade

Shade 1: Glass

Shade 1 Finish: Seeded Cloud

Shade 1 Top Width: 2"

Shade 1 Bottom L/W: 0" / 4"

Shade 1 Height: 10.75"

ELECTRICAL



Bulb 1

Bulb Included: No

Socket: E26 Medium Base

Bulb Type: A19

Max Wattage: 15

Bulb Quantity: 3

Wire Length: 144"

Cord Type: B & W TEFLON W/ GROUND WIRE

Gem Box Required (2"x3"): No

Dark Sky: No

SHIPPING

Carton 1: 26" x 26" x 15"

Carton 1 Weight: 22lb

Shipping Method: Ground

Country of Origin: VN

