Project / Job Name:

Location:

Fixture Type:

Notes:



67-137 - Remote Emergency Light; Low-Voltage Backup; Double Head, White Finish, Wet Location Rated

GENERAL	
Company	NUVO
EA Height	5.08
EA Width	6.57
EA Length	11.14
Bulb Included	Integrated
Material	Thermo Plastic
Fixture Type	Emergency Light
Includes	Mounting hardware and accessories
Product Notes	UL94V-0, Thermoplastic, -25C-50C
Status	Active
Style	Utility
Surge Protection	Built-in surge protection - 3KV
CCT Selectable	No
Wattage Selectable	No
Finish Family	White
Additional Info	Input Wattage: 2W; Output Wattage: 2W
Amps	0.667/0.167A
Mounting Diameter	4.5
Has Camera	No
IOT Enabled	No
Lens Finish	Clear
Lens Material	Polycarbonate (PC)
SDS Class	LED_Fixture
Indoor Outdoor	Indoor, Outdoor
Product Technology	LED
Fixture Lamp Count	2
Incandescent Equivalent	10W
Serviceable Battery	No
Battery Indicator	No
Digital Display	No

ELECTRICAL	
CCT (Kelvin Temp)	5700K
Dimmable	Non-Dimmable
CRI	70+
Operating Temp	-13F to +122F (-25C to +50C)
Lumens	200L
Volts	3V/12V
Watts	2W

PHYSICAL	
Lamp Base	Integrated
Finish	WHITE
ANSI Base	Integrated
Lamp Type	Integrated LED
Mounting Procedure	Ceiling/Wall

ADDITIONAL INFO	
Warranty	2-Years

PACKAGING	
UPC	045923670305
Case Cube	2.9384
Case Height	16.14
Case Length	22.83
Case Quantity	12
Case UPC	10045923670302
Case Weight	10.89
Case Width	13.78
EA Cube	0.2152
EA Height	5.08
EA Length	11.14
EA Quantity	1
EA Weight	0.89
EA Width	6.57
Pack Type	Box
Web Length	6.0
Web Width	9.5

COMPLIANCE	
CA Prop 65	Lead
FCC Compliant	No
Location Rating	Wet
ROHS Compliant	Yes
Safety Listing	cULus - Certified
California Ban	Lawful for sale
Title 20	Exempt
T24/JA8 Compliant	No

© Satco Products, Inc.
All rights reserved 2026