SWIFTWALL® CLICK

PRODUCT CATALOG

SWIFTWALL®

SWIFTWALL® CLICK



SwiftWall Click is a game-changer in modular wall systems, offering a fast, reusable, and effortless solution for temporary walls and rooms. Developed using our proprietary, patented technology, it requires no tools or special skills. Simply click the lightweight components together to easily install, reconfigure, remove, and relocate walls as needed.

Reimagine the way you create, divide, and transform space.



Panels

SwiftWall Click panels using our proprietary, patented technology, are designed for versatility across multiple applications, from isolating worksites to creating dynamic spaces in offices, events, or residential areas. Crafted from impact resistant, durable ABS, with an optional ASTM E-84 and NFPA 286 fire- and smoke-rated material, our panels help minimize noise with an STC21 sound rating. The non-hygroscopic, non-microbial panels are resistant to moisture and mold, making them ideal for any environment.

PRODUCT OVERVIEW

STANDARD SIZES: 8′ & 10′
All standard sizes are manufactured to
4′ wide by 1″ thick
(Custom sizes available)

WEIGHT
8′ : 42 lb
10′ : 53 lb

MATERIAL
ABS with aluminum joiners and polyisocyanurate core (Class A fire- and smoke-rated material available upon request)

FINISH OPTIONS
1. White light-sheen matte hair-cell ABS
2. Powder coated semi-gloss aluminum (Class A Only)

STANDARD PANELS

ANTI-SLIP GASKETS
Optional anti-slip gaskets available

Anti-slip Gasket: Top



Anti-slip Gasket: Bottom





SwiftWall Click sets a new benchmark for speed and simplicity. Infinitely configurable, it redefines what's possible.

Doors & Windows

Our selection of doors and windows can turn any SwiftWall structure into an office, conference room, or break room.

DOOR

SIZE
8′ or 10′ x 48″ wide
(34″ x 88″ entryway size)

WEIGHT
8′ = 68 lb | 10′ = 85 lb

MATERIAL
ABS with aluminum joiners and polyisocyanurate core (Class A fire-rated material available upon request)

INCLUDED HARDWARE
- Lock
- Handle

FINISH OPTIONS
1. White light-sheen matte hair-cell ABS
2. Powder coated semi-gloss aluminum (Class A Only)

HARDWARE OPTIONS
Panic Bar & Self Closer available but not shown

Lever Lock

Lever Keypad Lock

WINDOW OPTIONS

SIZE

Window
36″ x 36″

Window
46″ x 46″

Door Window
30″ x 30″

Corners & Intersections

These durable corners and intersections form a robust, rigid framework for any SwiftWall structure, allowing infinite configurations to bring your unique vision to life.

ROUNDED 90° CORNER

SIZE
2.188″ x 2.188″ x 8′
2.188″ x 2.188″ x 10′

WEIGHT
8′ = 12.7 lb | 10′ = 15.9 lb

MATERIAL
Industrial extruded aluminum

FINISH
Powder coated white, semi-gloss

ADJUSTABLE ANGLE CORNER

SIZE
1″ x 2.59″ x 8′
1″ x 2.59″ x 10′

WEIGHT
8′ = 10.8 lb | 10′ = 13.4 lb

MATERIAL
Industrial extruded aluminum

FINISH
Powder-coated white, semi-gloss

T-INTERSECTION

CLOSED JOINER SIZE
3.375″ x 2.125″ x 8′
3.375″ x 3.125″ x 10′

WEIGHT
8′ = 20.3 lb
10′ = 25.4 lb

MATERIAL
Industrial extruded aluminum

FINISH
Powder-coated white, semi-gloss

OPEN JOINER SIZE
3.375″ x 2.375″ x 8′
3.375″ x 2.75″ x 10′

WEIGHT
8′ = 18.1 lb
10′ = 22.6 lb

MATERIAL
ABS & Aluminum

FINISH
Hair-cell or Smooth

Joiners, Track & C-Channel OPTIONAL

L-JOINER

SIZE
2.125″ x 2.375″ x 8′
2.125″ x 2.375″ x 10′

WEIGHT
8′ = 14.4 lb | 10′ = 18 lb

MATERIAL
ABS & Aluminum

FINISH
Hair-cell or Smooth

X-JOINER

SIZE
3.375″ x 3.375″ x 8′
3.375″ x 3.375″ x 10′

WEIGHT
8′ = 24 lb | 10′ = 30 lb

MATERIAL
ABS & Aluminum

FINISH
Hair-cell or Smooth

TRACK

SIZE
3.5″ x 2.5″ x 10′ — Cut to length

WEIGHT
9.28 lb

MATERIAL
Industrial extruded aluminum

FINISH
Powder-coated white, semi-gloss

C-CHANNEL

SIZE
1.28″ x 1″ x 10′ — Cut to length
(8′, 12′, and 16′ C-Channels also available)

WEIGHT
3.7 lb

MATERIAL
Industrial extruded aluminum

FINISH
Powder-coated white, semi-gloss

Bracing OPTIONAL

SANDWICH BRACE

SIZE
28″ x 6″ x 18.125″

WEIGHT
13.6 lb

MATERIAL
Steel

FINISH
Powder-coated white, semi-gloss

POST BRACE

SIZE
28″ x 6″ x 17.25″

WEIGHT
20.2 lb

MATERIAL
Steel

FINISH
Powder-coated white, semi-gloss

CROSS-BRACE

SIZE
6′

WEIGHT
6 lb

MATERIAL
Steel

FINISH
Powder-coated white, semi-gloss



Bracing & Productivity Tools OPTIONAL

VERTICAL BRACE

SIZE
5.375″ x 18.95″ x 8′ to 10′ (adjustable)

WEIGHT
35.7 lb

MATERIAL
Steel

FINISH
Powder-coated white, semi-gloss



PANEL FOOT LIFT

Foot lift with tapered nose for easy placement

SIZE
12″ x 5.25″

MATERIAL
Durable Cast Aluminum

GRABO ELECTRIC PANEL LIFTER

Vacuum suction cup lifter includes battery, charger, carry bag and seal

SIZE
14″ x 10.9 ″ x 6″

WEIGHT
1 lb

FINISH
Black

SwiftWall Cart

FOLDABLE & STACKABLE CART

SIZE
30″ x 60″ x 57″ Tall

WEIGHT
120 lb

MATERIAL
Steel with aluminum tray

FINISH
White paint

FEATURES

Strap Style
2″ webbing with Velcro

Cart Capacity
2,800 lb

Casters
6″ x 2″
4 swivel casters with 2 rigid locking pins
2 wheel brakes

Maximum Panels on Cart
Flex: 10 panels
Click, Pro, Lite: 16 panels
Recommended to place tongue side down

Gasket Material
Provided for scratchproof cart stacking
Stackable up to 3 carts high

Foldable & Stackable

SwiftWall Kits

All SwiftWall products deploy rapidly and easily, but none more so than SwiftWall Kits®. Our kits can help mobilize your team quickly so you can focus on what you do best.

SWIFTWALL KITS

ROOM
40 Reconfigurable linear feet, 8′ or 10′ Tall

Potential Uses
8′ x 12′ Square
4′ x 16′ Square
2′ x 16′ U-Shape

MULTI-ROOM
96 Reconfigurable linear feet, 8′ or 10′ Tall

Potential Uses
(4) 8′ x 8′ Rooms
(2) 8′ x 8′ Rooms & (1) 12′ x 16′ Room
(2) 8′ x 8′ Rooms & (2) 8′ x 16′ Room

BARRIER
28 Reconfigurable linear feet, 8′ or 10′ Tall

Potential Uses
4′ x 16′ U-Shape
8′ x 8′ U-Shape
12′ x 12′ L-Shape

Other options available. | Class A fire-rated options available upon request.

Request a Demonstration

Contact us today to schedule a live demonstration and see firsthand how SwiftWall Click makes it all come together—effortlessly and with just a click!

SwiftWall.com | +1 989.279.023

SWIFTWALL® CLICK

Infinite Possibilities

Trusted by: Walmart LAX Google Turner GRAINGER SWINERTON

Learn More
SwiftWall.com
989.279.0232

MADE IN USA

SWIFTWALL®
CREATE. DIVIDE. TRANSFORM.