

GLADYS

HL1158201-AGB/CBV

Gladys rests with the ease of an artifact, serene and self-assured in simplicity. A smooth, rounded ceramic base in a soft, speckled Vanilla Bean glaze anchors the piece with a sense of solidity. An oversized brown handicraft hemp drum shade rises like a column with a woven texture that exhibits natural variations from piece to piece. Finished with Aged Brass hardware, Gladys is a cozy complement to modern spaces.

*Due to the one-of-a-kind nature of the medium, exact colors and patterns may vary slightly from the image shown.

FINISHES

AGED BRASS w/ Ceramic Vanilla Bean

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 20"

Width/Diameter: 10"

Canopy/Backplate: 7.5"

Product Weight: 5lb

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: No

Shade

Shade 1: Textile

Shade 1 Finish: Handicraft Hemp

Shade 1 Top Width: 9"

Shade 1 Bottom L/W: 0" / 10"

Shade 1 Height: 11"

ELECTRICAL



Bulb 1

Bulb Included: No

Socket: E26 Medium Base

Bulb Type: A19

Max Wattage: 15

Bulb Quantity: 1

Wire Length: 96"

Cord Type: SPT-2 BLACK FABRIC

Switch Type: ON/OFF SWITCH ON SOCKET

Gem Box Required (2"x3"): No

Dark Sky: No

SHIPPING

Carton 1: 15" x 15" x 25"

Carton 1 Weight: 11lb

Shipping Method: Ground

Country of Origin: VN

