Project / Job Name:

Location:

Fixture Type:

Notes:



65-656 - 40 Watt Small LED Wall Pack with Integrated Bypassable Photocell; CCT Selectable; 120-277 Volts; Dusk to Dawn Security Lighting; IP65; Bronze Finish

WET LOCATION · FC · RoHS COMPLIANT · CCT SELECTABLE · 50,000 HOURS · IP 65

GENERAL

Company	NUVO
EA Height	9.65
EA Width	9.84
EA Length	10.14
Bulb Included	Integrated
Extends (in)	7.45
Material	Aluminum / Polycarbonate (PC)
Fixture Type	Wall Pack
Status	Active
Style	Traditional
Surge Protection	Built-in surge protection - 2.5KV
Total Harmonic Distortion	<20%
CCT Selectable	Yes
Wattage Selectable	No
Finish Family	Bronze
Additional Info	IK10 Lens
Amps	0.333-0.144A
Has Camera	No
Integrated Features	Integrated Photocell
IOT Enabled	No
Photo Cell	Yes - Bypassable
Power Factor	>0.9
SDS Class	LED_Fixture
Indoor Outdoor	Outdoor
Product Technology	LED
Incandescent Equivalent	300W
Serviceable Battery	No
Battery Indicator	No
Digital Display	No

ELECTRICAL

CCT (Kelvin Temp)	3000K/4000K/5000K
Dimmable	Non-Dimmable
Hours Rated	50000
Beam Angle (degree)	80
Color Temp	Warm to Cool White
CRI	70+
Operating Frequency	50/60Hz
Operating Temp	-40F to +113F (-40C to +45C)
HID Equivalent	150W
Lumens	4200L-5000L
Volts	120V-277V
Watts	40W
Max Lumens	5000L
Connection	Hardwire

PHYSICAL

Lamp Base	Integrated
Finish	BRONZE
ANSI Base	Integrated
Lamp Type	Integrated LED
Mounting Procedure	Wall

ADDITIONAL INFO

Warranty	5-Years

FEATURES

Flicker Free	Yes

PACKAGING

UPC	045923651762
Case Cube	2.6229
Case Height	20.28
Case Length	20.28
Case Quantity	4
Case UPC	10045923651769
Case Weight	21.38
Case Width	11.02
EA Cube	0.5572
EA Height	9.65
EA Length	10.14
EA Quantity	1
EA Weight	5.35
EA Width	9.84
Pack Type	Box
Web Height	8.44
Web Width	8.5

COMPLIANCE

ADA Compliant	No
Bug Rating	B2-U3-G2
CA Prop 65	Lead
FCC Compliant	Yes
IP Rating	IP65
Location Rating	Wet
ROHS Compliant	Yes
Safety Listing	cULus - Certified
California Ban	Lawful for sale
DLC Approved	No
Title 20	Exempt
T24/JA8 Compliant	No

© Satco Products, Inc.
All rights reserved 2026