

## PRODUCT DESCRIPTION

### MEASUREMENTS

| | |
|---|---|
| DIMENSION | : 24" W x 32" H x 1.5" Ext |
| HANGING WEIGHT | : 36.3 lb |

### LAMPING

| | |
|---|---|
| INPUT VOLTAGE | : 120V |
| LUMENS | : 3,700 Rated (950 Del.) |
| BULB | : 1 x 37W LED PCB Integrated , 37W Total |
| BULB INCLUDED | : (Integrated) |
| DIMMABLE | : Dimmable on touch switch |
| CRI | : 90 CRI |
| COLOR_TEMP | : 3000-4000-5000K |
| LIGHTING_DIRECTION | : Indirect |

### FINISHES OPTION

Black (BK)
Gold (GLD)
Satin Nickel (SN)

### MATERIAL

Steel, Glass

### RATINGS

cETLus
Damp Location
CA Title 24

### ADDITIONAL

INSTALL UP/DOWN: Vertical / Hori
RATED LIFE 35000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com