Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____

PRODUCT DESCRIPTION

MEASUREMENTS

DIMENSION	: 13.75" L x 13.75" W x 5.5" H
MAX OAH	: 128" OAH
CANOPY	: 5" W x 1.25" H x 5" L
HANGING WEIGHT	: 3.75 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 1,000 Rated (970 Del.)
BULB	: 1 x 15W LED AC Intergrated , 15W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Triac or ELV
CRI	: 90 CRI
COLOR_TEMP	: 27-30-35-40-50K

MATERIAL

Gypsum, Steel, Acrylic

RATINGS

cETLus
Location

ADDITIONAL

RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com