



Technical Data

Color	Black
Sizes Available	S-2XL
Polymer	Butyl
Thickness	16 Mil
Lining	Unlined
Dip	Single
Length	11"
Cuff	Rolled
Grip	Smooth
Construction	Unsupported, Waterproof
Case Dimensions (in)	32.00 x 21.00 x 15.00
Case Weight (lbs)	60.01
Packed	288 Pair/Case
Packaging	Pair Bagged Plain
Certifications	TAA Compliant, Latex Free
Country of Origin	United States

North® Butyl™

16 Mil Butyl Rubber Glove with Smooth Grip - 11"

- Exceptional resistance to a broad range of toxic chemicals: making it the only suitable for many critical applications
- Highly resistant to ketones (MEK: MIBK: acetone) and esters (tricresyl phosphate: amyl acetate: ethyl acetate)
- Solvent based: multi-dip manufacturing process provides multiple layers of polymer (like a glove within a glove) which results in a glove of superior quality
- Butyl provides the highest permeation resistance to vapors and gases

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
B161/7	Black	S	821812008066	821812008059	00821812008042
B161/8	Black	M	821812008097	821812008080	00821812008073
B161/9	Black	L	821812008127	821812008110	00821812008103
B161/10	Black	XL	821812008004	821812007991	00821812007984
B161/11	Black	2XL	821812008035	821812008028	00821812008011