


LED recessed luminaire for machines



Product-Nr.	153010-12
EAN:	4260556625447
Model:	FIELDLED EVO Integrated, M12 rear-side







Order number:	153010-12
Model:	FIELDLED EVO Integrated, M12 rear-side
Type:	LED recessed luminaire for machines
Illuminant:	SMD LED
Power consumption:	~19 W
Lamp luminous flux:	3000 lm
Lamp luminous efficiency:	155 lm/W
Light distribution:	Direct
Light colour:	5700K 3-step MacAdam
Colour rendering (Ra):	>85
Supply voltage:	24V DC ± 10%
Connection (connector):	M12 A-coded, rear side
Degree of protection:	IP67/IP69K
Class of protection:	III
Glare control:	Microprisms
Beam angle (optics):	100°
Operating temperature:	-30 °C - +60 °C (-22 °F - 140 °F)
Storage temperature:	-30 °C - +80 °C (-22 °F - 176 °F)
Lamps lifetime:	> 100,000 h (L80/B10)
Vibration resistance:	At 10 to 55 Hz (amplitude 0.35 mm (~0,01“))
Shock resistance:	Up to 50 g (~2 oz)
Housing material:	aluminium
Cover material:	ESG (toughened tempered glass), shatterproof
Height [B] x Width [C]:	30 mm x 96 mm (~1.18" x ~3.78"), frame: 5.6 mm x 132 mm (~0.22" x ~5.2")
Length [A]:	280 mm (~11,02“)
Weight (net):	1180 g (~42 oz)
Gross weight:	1330 g (~47 oz)
Risk group (DIN EN 62471):	Free group
Markings:	CE, UKCA, ETL Listed (5003529)
Dimmable:	Optional via accessories
Made in:	Germany

Irrtümer, Systemfehler und Änderungen vorbehalten./
Errors and technical changes excepted. 30.9.2026

LED2WORK GmbH | Stuttgarter Straße 13 A | 75179 Pforzheim | Germany
T: +49 7231 44920-00 | info@led2work.com | www.led2work.com |
Shop.led2work.com