Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____

PRODUCT DESCRIPTION

MEASUREMENTS

DIMENSION	: 7.25" W x 7.25" H x 3" Ext
MAX OAH	: 5" W x 5" H
HANGING WEIGHT	: 0.9 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 400 Rated (310 Del.)
BULB	: 1 x 6W LED DC Integrated , 6W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Triac or ELV at 120V
CRI	: 90 CRI
COLOR_TEMP	: 27-30-35-40-50K
LIGHTING_DIRECTION	: Indirect

MATERIAL

Stone, Aluminum, Acrylic

RATINGS

cETLus
Location
ADA



ADDITIONAL

INSTALL UP/DOWN: Any
RATED LIFE 50000 Hours
OPERATING TEMPERATURE: -20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com