

CASPIAN

B2318-PBR

The Caspian family draws inspiration from soft hardware forms, translating sweeping metal lines into a tailored picture light. A continuous arm encases the tubular shade, balancing function with form. Finished in Patina Brass and available in two sizes, it casts a focused beam across artwork or architectural details.

FINISHES

PATINA BRASS

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 4.25"

Width/Diameter: 18.25"

Length: 7.75"

Canopy/Backplate: 6.5"

Product Weight: 6lb

Extension: 7.75"

Top to Center: 2.25"

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: No

Shade



ELECTRICAL



Bulb 1

Bulb Included: No

Socket: E26 Medium Base

Bulb Type: T10-5.5

Max Wattage: 10

Bulb Quantity: 2

Wire Length: 7"

Cord Type: B & W TEFLON W/ GROUND WIRE

Gem Box Required (2"x3"):

Dark Sky: No

SHIPPING

Carton 1: 24" x 13" x 5"

Carton 1 Weight: 8lb

Shipping Method: Ground

Country of Origin: VN