Project / Job Name:

Location:

Fixture Type:

Notes:



**67-139** - Emergency Light; Dual Head; 120/277 Volts; White Finish; Remote Compatible

## GENERAL

| | |
|---|---|
| Company | NUVO |
| EA Height | 9.06 |
| EA Width | 2.56 |
| EA Length | 4.72 |
| Bulb Included | Integrated |
| Material | Thermo Plastic |
| Fixture Type | Emergency Light |
| Includes | Mounting hardware and accessories |
| Product Notes | UL94V-0, Thermoplastic, 3.6V 900mAh Ni-Cad Battery, 90 minutes duration, 24 hour charge time, 10C-40C, Remote Compatible; Path of Egress: 6 Ft. |
| Status | Active |
| Style | Utility |
| Surge Protection | Built-in surge protection - 3KV |
| CCT Selectable | No |
| Wattage Selectable | No |
| Finish Family | White |
| Additional Info | Input Wattage: 1W; Output Wattage: 2.5W; Energy Used in Maintenance Mode: 1W |
| Amps | 0.008/0.004A |
| Has Camera | No |
| IOT Enabled | No |
| Lens Finish | Clear |
| Lens Material | Polycarbonate (PC) |
| SDS Class | LED_Fixture |
| Indoor Outdoor | Indoor |
| Product Technology | LED |
| Fixture Lamp Count | 2 |
| Incandescent Equivalent | 15W |
| Serviceable Battery | No |
| Battery Indicator | No |
| Digital Display | No |

## ELECTRICAL

| | |
|---|---|
| CCT (Kelvin Temp) | 5700K |
| Dimmable | Non-Dimmable |
| CRI | 70+ |
| Operating Frequency | 50/60Hz |
| Operating Temp | +50F to +104F (+10C to +40C) |
| Lumens | 210L |
| Volts | 120V/277V |
| Watts | 1W |
| Battery Chemistry | Ni-Cad |

## PHYSICAL

| | |
|---|---|
| Lamp Base | Integrated |
| Finish | WHITE |
| ANSI Base | Integrated |
| Lamp Type | Integrated LED |
| Mounting Procedure | Ceiling/Wall |

## ADDITIONAL INFO

| | |
|---|---|
| Warranty | 2-Years |

## PACKAGING

| | |
|---|---|
| UPC | 045923670299 |
| Case Cube | 0.8629 |
| Case Height | 10.83 |
| Case Length | 14.57 |
| Case Quantity | 12 |
| Case UPC | 10045923670296 |
| Case Weight | 11.38 |
| Case Width | 9.45 |
| EA Cube | 0.0634 |
| EA Height | 9.06 |
| EA Length | 4.72 |
| EA Quantity | 1 |
| EA Weight | 0.93 |
| EA Width | 2.56 |
| Pack Type | Box |
| Web Height | 4.38 |
| Web Length | 2.38 |
| Web Width | 8.25 |

## COMPLIANCE

| | |
|---|---|
| CA Prop 65 | Lead |
| FCC Compliant | Yes |
| Location Rating | Damp |
| ROHS Compliant | Yes |
| Safety Listing | cULus - Certified |
| California Ban | Lawful for sale |
| DLC Approved | No |
| Title 20 | Yes |
| T24/JA8 Compliant | No |



© Satco Products, Inc.
All rights reserved 2026