SIEMENS

Data sheet US2:E0204ML1060F



Siemens Energy Management Residential Specialty Load Centers: Small Circuit (2-10). Sub Brand: Load Centers Type: 1: Application: Residential: Voltage Rating: 120/240V Amperage Rating: 60A Phase: 1PH Load Regulation: 60A Wiring Configuration: 3w Bus Rating: 60A Interrupt Rating: 100000AIC. EQ LC 2S 4C ML 60A N1-F

General technical data	
configuration of the busbars	60A
fastening method	Flush
phase number	1
suitability for operation	Residential
Electricity	
ampacity	60 A
voltage between phase and Ground (GND) rated value	120 V
voltage between phase and phase rated value	240 V
Switching capacity	
switching capacity current acc. to EN 60898 rated value	100000 A
Model	
product brand name	Siemens
product sub brand name	Load Centers
product type designation	1
type of wiring of distribution board	3w
Mechanical Design	
number of modular width units for installation width	2
width [in]	1192.596 in

last modified: 1/6/2021

Subject to change without notice
© Copyright Siemens