



North®

Short Brim, Type I Non-Vented, Hard Hat with HDPE Shell, 4-Point Textile Suspension, Wheel Ratchet Adjustment and Optional 4-Point Chinstrap

- 4-Point textile suspension, with ratchet adjustment
- Dual-locking mechanism prevents the hard hat from coming loose
- Optional four-point chin strap available
- Lightweight yet durable HDPE shell

Technical Data

Color	White, Gray, Orange, Red, Black, Yellow, Green, Dark Blue
Sizes Available	OS
Packaging	Bagged Each
Packed	20/Case
Case Dimensions (in)	22.44 x 17.72 x 18.50
Case Weight (lbs)	21.38
Country of Origin	China
Shell Material	HDPE
Shell	Non-Vented
Brim Length	Standard
Size Adjustment	Wheel Ratchet
Certifications	ANSI/ISEA Z89.1, EN 397, CSA Z94.1 Certified

Performance Data

ANSI Type

Type I

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
NSB20011	Black	OS	883940433004		00883940433165
NSB20071	Dark Blue	OS	883940433028		00883940433189
NSB20009	Gray	OS	883940432991		00883940433158
NSB20004	Green	OS	883940432984		00883940433141
NSB20003	Orange	OS	883940432977		00883940433134
NSB20015	Red	OS	883940433011		00883940433172
NSB20001	White	OS	883940432953		00883940433110
NSB20002	Yellow	OS	883940432960		00883940433127