

Product Specifications



#10 x 3/4" Hex Washer Head Self Drilling Screw (1000pc Tuff Pail)

Part Number TEKHW1034TP1K

UPC 781002858591

Self-Drilling Screws are manufactured from cold-heading steel and feature a #2 drill point. The unique tip design allows them to drill, tap, and fasten metal to metal objects in one operation, without the need to pre-drill. This creates the optimal drill performance and thread forming experience. The most common applications are used on metal to metal, but they can also be used in a wide variety of other applications. IFI-113 and ASTM C954 cover the material and performance requirements for steel self-drilling screws.



Physical Characteristics

Type	Self Drilling Screw
Drive Type	Hex
Head Type	Hex Washer
Thread Type	BSD
Point Type	#3
Size	#10 x 3/4"
Dia./Thread Size	#10
Hex Size	5/16"
Head Diameter	0.414" to 0.384"
Length (in)	3/4"
Head Height	0.120" to 0.105"
Thread Pitch\Thread Per Inch	16
Material	Carbon Steel
Finish	Zinc Plated

Performance Data

Rockwell Hardness	HRC 32 - 40
Special Features	Drill, Taps and Fastens in One Operation
Applications	Metal to Metal

Packaging Details

Standard Qty	1000
Master Qty	6000
Price Per	100
Package Length	4.75
Package Width	5.50
Package Height	4.00
Package Weight	4.08

Certifications

UNSPSC	31161506
RoHS Compliant	Yes
Meets/Exceeds	IFI-113

L.H. Dottie Co. Commerce, CA 323-725-1000 www.lhdottie.com