



P65

Technical Data



Color	Clear
Sizes Available	OS
Packaging	Bagged Each
Packed	144 Pair/Case
Case Dimensions (in)	19.69 x 12.99 x 13.78
Case Weight (lbs)	8.60
Country of Origin	Taiwan
Lens	Clear
Frame Style	Rimless
Lens Color	Clear
Frame Fit	Universal
Lens Coating	FogLess 3Sixty, Anti-Scratch
Bridge	Molded
Base Curve	9.5
Construction	Metal Detectable
Certifications	ANSI Z87.1, TAA Compliant

Bouton® Optical Zenon Z12™

Rimless Safety Glasses with Blue Metal Detectable Temple, Clear Lens and Anti-Scratch / Fogless® 3Sixty™ Coating

- Lightweight, rimless design provides all day user comfort
- Thin, flexible temples provide a secure fit without uncomfortable pressure points
- Special nylon temples are metal detectable and X-Ray detectable
- Plated steel screws resist corrosion while providing metal detection properties
- FogLess® 3Sixty™ enhanced hydrophobic action resists lens fogging and provides clear vision in extreme working conditions
- Molded nose bridge design to fit the vast majority of users
- 9.5 Base curve lens
- Meets ANSI Z87.1+
- ⚠ **WARNING:** Reproductive Harm - www.P65Warnings.ca.gov

Applications

- General Manufacturing
- Construction Applications
- Indoor Work

SKU Information

SKU	FRAME COLOR	LENS	LENS		UPC	UPC (INNER)	UPC (CASE)
			LENS COLOR	COATING			
250-01-0000	Black	Clear	Clear	AS	616314024863	01616314024863	02616314024863
250-01-0001	Black	Tinted	Gray	AS	616314024870	01616314024870	02616314024870
250-01-0002	Black	I/O	Clear	AS	616314025297	01616314025297	02616314025297
250-01-0004	Black	Tinted	Orange	AS	616314022784	01616314022784	02616314022784
250-01-0005	Black	Mirror	Silver	AS	616314025280	01616314025280	02616314025280
250-01-0020	Black	Clear	Clear	AS/AF	616314025259	01616314025259	02616314025259
250-01-0021	Gray			AS/AF	616314067181	01616314067180	02616314067189
250-01-0021-LRS					616314271823	01616314271822	02616314271821
250-01-0080	Black	Clear	Clear	U	616314025266	01616314025266	02616314025266
250-01-0300	Clear	Clear	Clear	AS	616314232534	01616314232533	02616314232532
250-01-0320	Clear	Clear	Clear	AS	616314232541	01616314232540	02616314232549
250-01-0900	Clear	Clear	Clear	AS	616314022487	01616314022487	02616314022487
250-01-0902	Clear	I/O	Clear	AS	616314022517	01616314022517	02616314022517
250-01-0902-LRS					616314271816	01616314271815	02616314271814
250-01-0920	Clear	Clear	Clear	AS/AF	616314022494	01616314022494	02616314022494
250-01-0920-LRS					616314271809	01616314271808	02616314271807
250-01-0980	Clear	Clear	Clear	U	616314022500	01616314022500	02616314022500
250-01-5503	Light Blue	Tinted	Light Blue	AS	616314019999	01616314019999	02616314019999
250-01-5504	Dark Brown	Tinted	Dark Brown	AS	616314020001	01616314020001	02616314020001
250-01-5509	Amber	Tinted	Amber	AS	616314020018	01616314020018	02616314020018
250-01-D020	Clear	Clear	Clear	AF	616314357770	10616314357777	20616314357774
250-01-D053	Blue	Tinted	Light Blue	AF	616314357787	10616314357784	20616314357781
250-01-D520	Clear	Clear	Clear	FL360/AS	616314357756	10616314357753	20616314357750
250-01-D553	Blue	Tinted	Light Blue	FL360/AS	616314357763	10616314357760	20616314357767
250-01-F020	Black	Clear	Clear	AS/AF	616314164040	01616314164049	02616314164048
250-01-F021	Black	Tinted	Gray	AS/AF	616314165177	01616314165176	02616314165175
250-01-F022	Black	I/O	Clear	AS/AF	616314165184	01616314165183	02616314165182

KEY: AF = Anti-Fog / AR = Anti-Reflective / AS = Anti-Scratch / FL360 = Fogless 3Sixty / U = Uncoated