Highlander | E30223-99BK

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

An internally illuminated shadow box is encased in glass with a tartan plaid pattern engraved to mimic linen. The back plate features a polished stainless steel plate adding an almost infinite dimension to the pattern. Constructed of aluminum in Matte Black finish and 304 grade Stainless Steel, the product is also suitable for installations outdoors.



MEASUREMENTS

DIMENSION	: 6" W x 30" H x 1.75" Ext
BACK PLATE	: 6" W x 30" H x 15" HCO
HANGING WEIGHT	: 5.72 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 2,500 Rated (1,350 Del.)
BULB	: 1 x 45.5W LED AC Integrated , 46W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Triac CL
CRI	: 90 CRI
COLOR_TEMP	: 3000K
LIGHTING_DIRECTION	: Indirect

FINISHES OPTION

Black (BK)

GLASS

Linen Patterned 99

MATERIAL

Aluminum, Glass

RATINGS

cETLus
Wet Location
ADA

ADDITIONAL

INSTALL UP/DOWN: Any
RATED LIFE 30000 Hours
OPERATING TEMPERATURE: -20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com