
Discus | E14353-RLGM

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

Discus brings the elemental beauty of natural stone to a clean, sculptural wall form. Circular slabs of travertine are softly backlit, allowing texture, pitting, and organic variation to become part of the illumination. White Travertine pairs with an Antique Bronze finish for a warmer expression, while Rosso Laterite and Black Basalt are set against a durable Gunmetal outdoor powder coat. Wet rated for indoor or outdoor use, ADA compliant, and offered in three sizes, Discus creates a quiet halo of light with architectural simplicity.



MEASUREMENTS

DIMENSION	: 10.25" W x 10.25" H x 3" Ext
MAX OAH	: 5" W x 5" H
HANGING WEIGHT	: 1.6 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 1,100 Rated (1,060 Del.)
BULB	: 1 x 11W LED DC Integrated , 11W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Triac or ELV at 120V
CRI	: 90 CRI
COLOR_TEMP	: 27-30-35-40-50K
LIGHTING_DIRECTION	: Indirect

FINISHES OPTION

Lava / Gunmetal (LVGM)
Rosso Laterite / Gunmetal (RLGM)
Travertine / Antique Bronze (TVANB)

MATERIAL

Stone, Aluminum, Acrylic

RATINGS

cETLus
Wet Location
ADA

ADDITIONAL

INSTALL UP/DOWN: Any
RATED LIFE 50000 Hours
OPERATING TEMPERATURE: -20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com