



320A 7J RGLS 1POS LVRBPS MS OH/UG-SW

cable entry type	OH/UG
fastening method	SURFACE MOUNTING
number of openings	9
suitability for operation	COMMERCIAL
ampacity	320 A
supply voltage frequency rated value 50/60 Hz	No
product brand name	TALON
product type designation	HQSW
special product feature	W/ LEVER BYPASS
design of the terminal strip	7 TERMINALS
certificate of suitability	UL

last modified:

4/9/2020 