Project / Job Name:

Location:

Fixture Type:

Notes:



SF77-325 - Single Plastic Flood Light With Round Plate For Dual Mounting And Ground Stake With 6 ft. Cord - Green Finish

WET LOCATION | 120 VOLT

GENERAL

Company	NUVO
EA Height	7.25
EA Width	4.0
EA Length	3.0
Bulb Included	No
Extends (in)	5.75
Material	Plastic
Fixture Type	Flood Light
Product Notes	6' green 8/2 SJTW wire
Status	Active
Style	Utility
Wire Length	72.0
CCT Selectable	No
Finish Family	Green
Amps	1.250A
Has Camera	No
IOT Enabled	No
Indoor Outdoor	Outdoor
Product Technology	Lamp Dependent
Fixture Lamp Count	1
Serviceable Battery	No
Battery Indicator	No
Digital Display	No

ELECTRICAL

Dimmable	Non-Dimmable
Volts	120v
Watts	150W
Connection	Plug In

PHYSICAL

Lamp Base	Medium
Finish	Green
ANSI Base	E26
Lamp Type	PAR38
Mounting Procedure	Landscape

ADDITIONAL INFO

Warranty	1-Year

PACKAGING

UPC	045923773259
Case Cube	0.7314
Case Height	15.25
Case Length	9.75
Case Quantity	12
Case UPC	10045923773256
Case Weight	9.26
Case Width	8.5
EA Cube	0.0503
EA Height	7.25
EA Length	3.0
EA Quantity	1
EA Weight	0.71
EA Width	4.0
Pack Type	Color Box
Web Height	3.0
Web Length	4.0
Web Width	3.0

COMPLIANCE

ADA Compliant	No
CA Prop 65	Diisononyl Phthalate (DINP)
Location Rating	Wet
ROHS Compliant	No
Safety Listing	UL - Certified
California Ban	Lawful for sale
DLC Approved	No
Title 20	Exempt
T24/JA8 Compliant	No

© Satco Products, Inc.
All rights reserved 2026