



022-5292

Northstar Coastal Edge 20' SS Cable SRL

FEATURES :

- Exclusive cable retraction limiter
- Simplified cable replacement system
- Semi-sealed mainspring
- Semi-sealed pawl assembly
- Oscillating, double-locking/anti-ratcheting pawls
- 360/180° swivel attachment point w/alu carabiner
- Lifeline handle w/ mini absorber and indicating stainless steel swivel snap hook
- RFID equipped for easy asset tracking
- All components are Z359.12 compliant

Eligible for service and repair

Class

2

Anchor above or below dorsal D-ring



USER WEIGHT CAPACITY	
ANSI	130-310 lbs. (59-141 kg)
OSHA	Up to 420 lbs. (191 kg)

STANDARD COMPLIANT WITH	
ANSI	Z359.14-2021
OSHA	1910.140, 1910.66

ANSI CLASS 1	
Max. arrest force	≤ 1,800 lbs. (817 kg)
Avg. arrest force	≤ 1,350 lbs. (612 kg)
Max. arrest distance	≤ 42 in. (107 cm)
Actual arrest distance	≤ 41 in. (104 cm)
Max. free fall distance	24 in. (61 cm)
Min. required fall clearance	6 ft. 11 in. (2.1 m)
For full clearance requirements, see user instructions	

ANSI CLASS 2	
Max. arrest force	≤ 1,800 lbs. (817 kg)
Avg. arrest force	≤ 1,350 lbs. (612 kg)
Max. arrest distance	N/A
Actual arrest distance	92 in. (234 cm)
Max. free fall distance	72 in. (183 cm)
Min. required fall clearance	16 ft. 2 in. (4.9 m)
For full clearance requirements, see user instructions	

MATERIAL SPECIFICATION	
Cable	13/64" stainless steel
Carabiner	Aluminum
Housing	Polycarbonate
Load-Indicating Swivel Snap Hook	Stainless steel
Shock pack	Polyester



022-5292

Northstar Coastal Edge 20' SS Cable SRL



Standards: ANSI Z359.14-2021
OSHA 1910.140, 1910.66

Capacity: ANSI 130-310 lbs. (59-141 kg)
OSHA Up to 420 lbs. (191kg)

CONNECTOR

ATTACHMENT

Part Number	Single Leg (S) / Dual Leg (D) SRL Class	Working Length (ft.)	Lifeline Material	Lifeline Dimensions (in.)	Housing Material	Weight (lbs.)	Steel Snap Hook	Steel Swivel Snap Hook	Stainless Steel Swivel Snap Hook	Dielectric Snap Hook	ALU Snap Hook	U-Steel Swivel Snap Hook	Steel Rebar Hook	Steel Swivel Rebar Hook	ALU Swivel Rebar Hook	Steel Captive Eye Carabiner	ALU Captive Eye Carabiner	ALU Swivel Carabiner	No Attachment	Tip Lock Steel Carabiner	Steel Carabiner	ALU Captive Eye Carabiner	ALU Carabiner	ALU Snap Hook	ALU Swivel Snap Hook	ES-EX313	Cab Mount Bracket	Soft Loop	Integrated B/WB	10:1 B/WB	90:1 B/WB	90:13 B/WB	
022-5292	1, 2 S	20	S.S. Cable	Ø13/64	Nylon	10.6						x										x											
022-5293	1, 2 S	30	S.S. Cable	Ø13/64	Nylon	12.8						x										x											
022-5294	1, 2 S	50	S.S. Cable	Ø13/64	Nylon	17.4						x										x											

