



P65

Technical Data



Color	Gray
Sizes Available	OS
Packaging	Bagged Each
Packed	144 Pair/Case
Case Dimensions (in)	24.92 x 10.00 x 12.40
Case Weight (lbs)	14.55
Country of Origin	Taiwan
Lens	Tinted
Frame Style	Foam-Lined
Lens Color	Light Gray
Frame Fit	Universal
Lens Coating	FogLess 3Sixty, Anti-Scratch
Bridge	Rubber
Temple	Co-Molded, Rubber Tips
Base Curve	9
Certifications	ANSI Z87.1, TAA Compliant

Bouton® Optical Fortify™

Rimless Safety Glasses with Gray Frame, Light Gray Lens, Foam Padding and Anti-Scratch/FogLess® 3Sixty™ Coating

- Lightweight, comfortable foam-sealed design keeps out dust & airborne particles
- Flexible co-injected temples provide a secure fit
- Non-slip rubber nose pads provide a comfortable fit
- FogLess® 3Sixty™ enhanced hydrophobic action resists lens fogging and provides clear vision in extreme working conditions
- 9 Base curve lens
- Meets ANSI Z87.1+
- **WARNING:** Reproductive Harm - www.P65Warnings.ca.gov

Applications

- Dusty Work Areas
- Outdoor Work
- Construction Applications
- Public Works

SKU Information

SKU	FRAME COLOR	LENS	LENS COLOR	LENS	UPC	UPC (INNER)	UPC (CASE)
				COATING			
250-54-0020	Gray	Clear	Clear	AS/AF	616314232503	01616314232502	02616314232501
250-54-0021	Gray	Tinted	Gray	AS/AF	616314232510	01616314232519	02616314232518
250-54-0024	Gray	IR Filter	Green	AF	616314267291	01616314267290	02616314267299
250-54-0520	Gray	Clear	Clear	AS/FL360	616314232527	01616314232526	02616314232525
250-54-0551	Gray	Tinted	Light Gray	FL360/AS	616314250224	01616314250223	02616314250222

KEY: AF = Anti-Fog / AR = Anti-Reflective / AS = Anti-Scratch / FL360 = Fogless 3Sixty / U = Uncoated