



## Low-Profile VGA High-Resolution RGB Coaxial Cable (HD15 M/M)), 6 ft.

MODEL NUMBER: **P502-006-SM**

Allows a high-resolution connection between your VGA-enabled computer and monitor up to 6 ft. apart with no ghosting.

### Description

The P502-006-SM VGA Coaxial High-Resolution Monitor Cable (M/M) allows you to connect your VGA-enabled computer and monitor up to six feet apart. Constructed from mini-coaxial (RGB) and paired video wire, it supports video resolutions up to 2048 x 1536, including 1080p, with no ghosting. It's more than 40% smaller in diameter than standard VGA cables, which increases airflow in tight spaces and makes it easier to install around corners.

Foil and braid shielding delivers reliable, error-free signal quality and protection from EMI/RFI line noise that can distort or destroy data. Molded HD15 male connectors with gold-plated contacts provide maximum conductivity and minimize data loss. Integral strain relief gives the cable extra flexibility, reduces stress, and helps the cable and connectors move freely without cracking.

### Features

#### Allows Connection Between VGA-Enabled Computer and Monitor Up to 6 ft.

- Supports video resolutions up to 2048 x 1536, including 1080p
- Made from mini-coaxial (RGB) and paired video wire
- Foil and braid shielding protects against EMI/RFI line noise that can distort or destroy data
- Molded HD15 male connectors and gold-plated contacts provide maximum conductivity and minimize data loss
- Integral strain relief protects cable and connectors from stress and cracking
- Rugged PVC jacket designed for long life

#### Special Slim Design

- More than 40% smaller in diameter than standard VGA cable
- Increases airflow in tight spaces
- Increased flexibility for installing around corners

## Specifications

OVERVIEW	
UPC Code	037332163271
INPUT	
Cable Length (ft.)	6

### Highlights

- Supports video resolutions up to 2048 x 1536, including 1080p
- Made from mini-coaxial (RGB) and paired video wire
- Foil and braid shielding blocks hazardous EMI/RFI line noise
- Gold-plated contacts for maximum conductivity
- Over 40% slimmer than standard VGA cables

### System Requirements

- Display device with HD15 input
- Computer with HD15 output

### Package Includes

- P502-006-SM Low-Profile VGA Coaxial High-Resolution Monitor Cable (M/M), 6 ft.



Cable Length (m)	1.8
<b>PHYSICAL</b>	
Color	Black
Shipping Dimensions (hwd / cm)	0.25 x 12.95 x 22.10
Shipping Dimensions (hwd / in.)	0.10 x 5.10 x 8.70
Shipping Weight (kg)	0.05
Shipping Weight (lbs.)	0.10
<b>CONNECTIONS</b>	
Side A - Connector 1	HD15 (MALE) - LOW PROFILE
Side B - Connector 1	HD15 (MALE) - LOW PROFILE
<b>FEATURES &amp; SPECIFICATIONS</b>	
Technology	Coax; VGA/SVGA
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>