

# Thin wall conduit fittings (for EMT conduit)

Set screw type fittings – zinc die cast

## SET SCREW TYPE FITTINGS – ZINC DIE CAST

### Features:

- Tri-head set screw may be installed using a slotted, Phillips or Robertson head screwdriver
- Concrete tight when taped
- Threadless

### Standard material:

- Zinc

### Standard finish:

- Natural

### Straight connectors – insulated

UL File No. E-22132



1450DC

1455DC



Cat. #	Size	Unit qty.	Wt. lbs. per 100
1450DC	1/2"	50	5
1451DC	3/4"	25	8
1452DC	1"	25	11
1453DC <sup>A</sup>	1 1/4"	10	20
1454DC <sup>A</sup>	1 1/2"	10	25
1455DC <sup>A</sup>	2"	5	37
1456DC <sup>A C</sup>	2 1/2"	12	59
1457DC <sup>A C</sup>	3"	12	78
1458DC <sup>A C</sup>	3 1/2"	6	101
1459DC <sup>A C</sup>	4"	6	120

<sup>A</sup> Two tightening screws.

<sup>C</sup> UL E-19189 and cUL Listed for EMT, IMC and rigid conduit.

### Straight connectors – non-insulated

UL File No. E-22132



1450DC

1455DC



Cat. #	Size	Unit qty.	Wt. lbs. per 100
450DC	1/2"	50	5
451DC	3/4"	25	7
452DC	1"	25	11
453DC <sup>A</sup>	1 1/4"	10	21
454DC <sup>A</sup>	1 1/2"	10	25
455DC <sup>A</sup>	2"	5	36
456DC <sup>A B</sup>	2 1/2"	12	58
457DC <sup>A B</sup>	3"	12	77
458DC <sup>A B</sup>	3 1/2"	6	98
459DC <sup>A B</sup>	4"	6	117

<sup>A</sup> Two tightening screws.

<sup>B</sup> UL and cUL Listed for EMT, IMC and rigid conduit.

## Couplings

UL File No. E-22132



1450DC

1455DC



Cat. #	Size	Unit qty.	Wt. lbs. per 100
460DC	1/2"	50	5
461DC	3/4"	25	7
462DC	1"	20	13
463DC <sup>B</sup>	1 1/4"	10	18
464DC <sup>B</sup>	1 1/2"	10	28
465DC <sup>B</sup>	2"	5	36
466DC <sup>B C</sup>	2 1/2"	12	64
467DC <sup>B C</sup>	3"	12	81
468DC <sup>B C</sup>	3 1/2"	6	98
469DC <sup>B C</sup>	4"	6	116

<sup>B</sup> Four tightening screws.

<sup>C</sup> UL and cUL Listed for EMT, IMC and rigid conduit.

## Offset connectors – non-insulated

UL File No. E-22132



Cat. #	Size	Unit qty.	Wt. lbs. per 100
2400	1/2"	10	11
2401	3/4"	10	18
2402	1"	10	25