



Project / Job Name:

Location:

Fixture Type:

Notes:

S29898 - 7 Watt PLC LED; 27K/3K/35K/4K CCT; GX32d Base; Omni; Type A/B; 120-277 Volt



GENERAL

Company	SATCO
EA Height	5.83
EA Width	1.61
EA Length	1.61
Lamp Ballast Type AB	Type A/B
Lamp Filament	LED
Material	Plastic / Aluminum
Fixture Type	Miniature
Status	Active
Surge Protection	Built-in-surge protection - 0.5KV
Total Harmonic Distortion	<25%
CCT Selectable	Yes
Wattage Selectable	No
Finish Family	White
Amps	0.060/0.026A
IOT Enabled	No
Lens Finish	Frost
Lens Material	Polycarbonate (PC)
Lensed	Yes
Minimum Compartment Size	Length 11.81 in. Width 6.31 in. Height: 2.75 in.
Operating Position	Universal
Power Factor	>0.9
SDS Class	LED_Lamp
Indoor Outdoor	Indoor
Product Technology	LED
Fluor Equiv	22W

ELECTRICAL

CCT (Kelvin Temp)	2700K/3000K/3500K/4000K
Dimmable	Non-Dimmable
Hours Rated	50000
Beam Angle (degree)	360
Color Temp	Warm to Cool White
CRI	80+
Operating Frequency	50/60Hz
Operating Temp	-4F to +113F (-20C to +45C)
Lumens	900L
Volts	120V-277V
Watts	7W

PHYSICAL

Lamp Base	GX32d (2-Pin)
Finish	WHITE
Housing Color	White
ANSI Base	GX32d
Lamp Type	PLC
MOD Lamps	1.5
MOL	5.7

ADDITIONAL INFO

Warranty	5-Years
Rated For Enclosed Fixture	Yes

FEATURES

Flicker Free	No
--------------	----

PACKAGING

UPC	045923298981
Case Cube	0.2837
Case Height	6.8
Case Length	10.3
Case Quantity	24
Case UPC	10045923298988
Case Weight	6.2
Case Width	7.0
EA Cube	0.0087
EA Height	5.83
EA Length	1.61
EA Quantity	1
EA Weight	0.23
EA Width	1.61
Pack Type	Color Box
Web Length	5.7
Web Width	1.5

COMPLIANCE

Air Tight	No
CA Prop 65	Lead
Dark Sky Rated	No
FCC Compliant	Yes
IP Rating	IP20
Location Rating	Damp
NSF Approved	Yes
ROHS Compliant	Yes
Safety Listing	cULus - Certified
Title 20	Exempt
T24/JA8 Compliant	No