
Brink | E41510-WT

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

Brink brings quiet architectural drama to outdoor lighting through a clean rectangular form and a softly illuminated recessed channel. Finished in Matte Black or White, the design conceals its LED source within a horizontal reveal, allowing light to wash gently across the surface with subtle depth and control. Offered as both a wall sconce and coordinating step light, Brink creates a cohesive exterior lighting story for entries, pathways, stairs, and modern outdoor spaces. Minimal, durable, and refined, it turns a simple line of light into a striking design detail.



MEASUREMENTS

DIMENSION	: 5" W x 3.25" H x 0.75" Ext
BACK PLATE	: 5" W x 3.25" H
HANGING WEIGHT	: 0.57 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 300 Rated (20 Del.)
BULB	: 1 x 3W LED DC Integrated , 3W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Triac or ELV at 120V
CRI	: 90 CRI
COLOR_TEMP	: 27-30-40K
LIGHTING_DIRECTION	: Down

FINISHES OPTION

- Architectural Bronze (ABZ)
- Black (BK)
- White (WT)

MATERIAL

Aluminum, Plastic

RATINGS

cETLus
Wet Location

ADDITIONAL

INSTALL UP/DOWN: Down
RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com