Bubble | E51022-10WT

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____









PRODUCT DESCRIPTION

Double bubble, this series of flush mounts feature a Clear acrylic shade that encases an internal frosted shade. Integrated LED technology evenly illuminates the inner shades available in two sizes.





MEASUREMENTS

DIMENSION	: 18" L x 18" W x 4" H
CANOPY	: 13.75" W x 0.5" H x 13.75" L
HANGING WEIGHT	: 4.23 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 1,920 Rated (1,680 Del.)
BULB	: 1 x 24W LED AC Integrated , 24W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: ELV
CRI	: 90 CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

White (WT)

GLASS

Clear and White 10

MATERIAL

Steel,Acrylic

RATINGS

cETLus
DRY Location

ADDITIONAL

RATED LIFE 25000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com