



<b>EAN:</b>	4013288101280	<b>Size:</b>	110x15x15 mm
<b>Part number:</b>	05104603001	<b>Weight:</b>	23 g
<b>Article number:</b>	849 HSS	<b>Country of origin:</b>	CN
		<b>Customs tariff number:</b>	82075060

- Twist drill bit for wood applications
- Hex shaft for very good power transfer
- HSS = high speed steel with split point
- Finely-tuned material elasticity for great durability
- Very good concentricity

High quality wood twist drill bits for precise, splinter-free drilling in soft wood, hard wood and laminated panel material. Made out of high speed steel (HSS). The hexagonal shaft ensures very good power transfer. A finely-tuned material elasticity provides for a long service life. Very good concentricity. 1/4" drive suitable for holders as per DIN ISO 1173-D 6.3.

**Web link**

<https://www.wera.de/en/05104603001>

Wera - 849 HSS

05104603001 - 4013288101280

Wera Werkzeuge GmbH

Korzter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: [info@wera.de](mailto:info@wera.de)




### Twist drill bits for wood applications



Twist drill bits - for wood applications

- 1/4" drive suitable for holders as per DIN 3126-D 6.3 (ISO 1173)
- Hexagon shaft for very high torque transfer
- HSS = high speed steel
- Finely adjusted material elasticity for long service life
- Excellent concentricity
- Tough-absorbing tempered bits for particularly long service life

### Further versions in this product family:

			
	mm	mm	mm
05104600001	3.0	32.00	70.0
05104601001	4.0	32.00	74.0
05104602001	5.0	43.00	85.0
<b>05104603001</b>	<b>6.0</b>	<b>45.00</b>	<b>95.0</b>
05104604001	8.0	60.00	110.0
05104605001	10.0	70.00	120.0

### Web link

<https://www.wera.de/en/05104603001>

Wera - 849 HSS  
05104603001 - 4013288101280

Wera Werkzeuge GmbH  
Korzter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)