



PIP® Wolfjaw™

Full Brim Smooth Dome Hard Hat with Fiberglass Resin Shell, 8-Point Riveted Textile Suspension and Wheel-Ratchet Adjustment

- Fiberglass resin shell withstands radiant temperatures up to 350° F
- Smooth dome shape with exposed rivets is popular in Construction, Industry and Metalworking
- 8-Point riveted textile suspension for increased comfort and force displacement
- Durable wheel adjustment system for one hand size adjustments
- Soft, non-chaffing, EVA moisture management sweatband padding for maximum sweat absorption
- Three position height adjustment settings to ensure proper depth

Applications

- Mining
- Tunneling
- Demolition
- Utility Work
- Metalworking

Technical Data

Color	Black, Natural Brown, White, Yellow, Green
Sizes Available	OS
Packaging	Boxed
Packed	12/Case
Case Dimensions (in)	24.02 x 14.17 x 22.83
Case Weight (lbs)	19.62
Country of Origin	China
Shell Material	Fiberglass Composite
Shell	Non-Vented
Brim Style	Full
Brim Length	Standard
Size Adjustment	Wheel Ratchet
Suspension	Polyester Textile Straps
Sweatband	Felt Lined Foam
Size Range	53cm-63cm
Certifications	ANSI/ISEA Z89.1

Performance Data

ANSI Type	Type I
Electrical Class	Class G

Care Instructions

The unit may be cleaned with soap and warm water and dried with a soft cloth. The helmet should not be cleaned with chemical or abrasive cleaners. The helmet should be stored out of direct sunlight, away from chemicals and not exposed to extremes of temperature.

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
280-HP1481R-11M	Black	OS	616314376276	10616314376273	20616314376270
280-HP1481R-04	Green	OS	198987098322	10198987098329	20198987098326
280-HP1481R-81	Natural Brown	OS	616314376313	10616314376310	20616314376317
280-HP1481R-01	White	OS	616314376351	10616314376358	20616314376355
280-HP1481R-02	Yellow	OS	616314383786	10616314383783	20616314383780