

## Accessory kits and covers (continued)

| Old PRS catalog number | NAED/UIC number | New PRX catalog number | NAED/UIC number | Description                                                 |
|------------------------|-----------------|------------------------|-----------------|-------------------------------------------------------------|
| 2NK225                 | 786685436999    | 2NK225                 | 786685436999    | 200% neutral for 225 A panelboard ②                         |
| 1NK400                 | 786687011064    | 1NK400                 | 786687011064    | 200% neutral for 400/600 A panelboard ②                     |
| ISOGROUND              | 782116064007    | ISOGROUND              | 782116064007    | Insulated/isolated ground bar ②                             |
| CUGROUND               | 786685584515    | CUGROUND               | 786685584515    | 42–48 CKT Cu ground bus assembly ②                          |
| SRK                    | 786685584522    | SRK                    | 786685584522    | Series rating kit ②                                         |
| SEKB                   | 786689023515    | SEKB                   | 786689023515    | Service entrance barrier kit for BAB breaker with SEK 1/2 ② |

① Non-interchangeable.

② No physical change to product.

## Boxes and trims

| Old PRS catalog number | NAED/UIC number | New PRX catalog number | NAED/UIC number | Description                                                            |
|------------------------|-----------------|------------------------|-----------------|------------------------------------------------------------------------|
| EZB2036RBS             | 782116895922    | EZB2036RBS             | 782116895922    | EZ Box™ stocking 20 inches W x 36 inches H                             |
| EZB2042RBS             | 782116895939    | EZB2042RBS             | 782116895939    | EZ Box stocking 20 inches W x 42 inches H                              |
| EZB2048RBS             | 782116895946    | EZB2048RBS             | 782116895946    | EZ Box stocking 20 inches W x 48 inches H                              |
| EZB2060RBS             | 782116895953    | EZB2060RBS             | 782116895953    | EZ Box stocking 20 inches W x 60 inches H                              |
| EZB2072RBS             | 782116895960    | EZB2072RBS             | 782116895960    | EZ Box stocking 20 inches W x 72 inches H                              |
| EZB2090RBS             | 782116895977    | EZB2090RBS             | 782116895977    | EZ Box stocking 20 inches W x 90 inches H                              |
| EZT2036S               | 782116934201    | EZT2036S               | 782116934201    | EZ Trim™ surface unvented for 20 inches W x 36 inches H box WEM2 keyed |
| EZT2036F               | 782116934195    | EZT2036F               | 782116934195    | EZ Trim flush unvented for 20 inches W x 36 inches H box WEM2 keyed    |
| EZT2042S               | 786685399256    | EZT2042S               | 786685399256    | EZ Trim surface unvented for 20 inches W x 42 inches H box WEM2 keyed  |
| EZT2042F               | 786685400044    | EZT2042F               | 786685400044    | EZ Trim flush unvented for 20 inches W x 42 inches H box WEM2 keyed    |
| EZT2048S               | 782116934225    | EZT2048S               | 782116934225    | EZ Trim surface unvented for 20 inches W x 48 inches H box WEM2 keyed  |
| EZT2048F               | 782116934218    | EZT2048F               | 782116934218    | EZ Trim flush unvented for 20 inches W x 48 inches H box WEM2 keyed    |
| EZT2060S               | 782116934249    | EZT2060S               | 782116934249    | EZ Trim surface unvented for 20 inches W x 60 inches H box WEM2 keyed  |
| EZT2060F               | 782116934232    | EZT2060F               | 782116934232    | EZ Trim flush unvented for 20 inches W x 60 inches H box WEM2 keyed    |
| EZT2072S               | 782116934263    | EZT2072S               | 782116934263    | EZ Trim surface unvented for 20 inches W x 72 inches H box WEM2 keyed  |
| EZT2072F               | 782116934256    | EZT2072F               | 782116934256    | EZ Trim flush unvented for 20 inches W x 72 inches H box WEM2 keyed    |
| EZT2090S               | 786685355412    | EZT2090S               | 786685355412    | EZ Trim surface unvented for 20 inches W x 90 inches H box WEM2 keyed  |
| EZT2090F               | 786685355429    | EZT2090F               | 786685355429    | EZ Trim flush unvented for 20 inches W x 90 inches H box WEM2 keyed    |
| GWPBQ2036PR            | 782116064014    | GWPBQ2036PR            | 782116064014    | NEMA® 12/3R enclosure PRL1A/2A 20 inches W x 36 inches H               |
| GWPBQ2042PR            | 786685400051    | GWPBQ2042PR            | 786685400051    | NEMA 12/3R enclosure PRL1A/2A 20 inches W x 42 inches H                |
| GWPBQ2048PR            | 782116064021    | GWPBQ2048PR            | 782116064021    | NEMA 12/3R enclosure PRL1A/2A 20 inches W x 48 inches H                |
| GWPBQ2060PR            | 782116064038    | GWPBQ2060PR            | 782116064038    | NEMA 12/3R enclosure PRL1A/2A 20 inches W x 60 inches H                |
| GWPBQ2072PR            | 782116064045    | GWPBQ2072PR            | 782116064045    | NEMA 12/3R enclosure PRL1A/2A 20 inches W x 72 inches H                |
| GWPBQ2090PR            | 786687011132    | GWPBQ2090PR            | 786687011132    | NEMA 12/3R enclosure PRL1A/2A 20 inches W x 90 inches H                |

## Interrupting rating chart

| Main breakers |                |               |             | Voltage |       |       |
|---------------|----------------|---------------|-------------|---------|-------|-------|
| Series C/G    | Power Defense™ | Breaker frame | kAIC rating | 240 V   | 480 V | 600 V |
| EDB           | PDD23F ①       | PD2           | F           | 35      | —     | —     |
| ED            | PDD23G ①       | PD2           | G           | 65      | —     | —     |
| DK            | PDD33G ①       | PD3           | G           | 65      | —     | —     |
| FD            | PDG23G         | PD2           | G           | 65      | 35    | 18    |
| HFD           | PDG23M         | PD2           | M           | 100     | 65    | 25    |
| KD            | PDG33G         | PD3           | G           | 65      | 35    | 18    |
| HKD           | PDG33M         | PD3           | M           | 100     | 65    | 35    |
| LG            | PDG33G         | PD3           | G           | 65      | 35    | 18    |

① 240 V maximum.

## Breaker kit legend

| Breaker kit        | Domestic or global     | Frame type     | AIC rating | Breaker ampere rating | Mounting                  |
|--------------------|------------------------|----------------|------------|-----------------------|---------------------------|
| BK—<br>Breaker kit | D—<br>Domestic (240 V) | 2—PD2          | F<br>G     | — — — —Frame amperes  | Convertible or B = Bottom |
|                    | G—<br>Global (600 V)   | 2—PD2<br>3—PD3 | G<br>M     | — — — —Frame amperes  |                           |

Note: Example—BKD2G100

Compliances, specifications and availability are subject to change without notice. Please contact your Eaton representative for availability.

Eaton  
1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
Eaton.com

© 2021 Eaton  
All Rights Reserved  
Printed in USA  
Publication No. SA014045EN / Z24851  
February 2021

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

