

ARCATA

F2040-VGL

A fresh take on a botanic motif, the Arcata family features sculptural, romantic silhouettes with highly tactile, hand-worked finishes. The gentle sweeping arms transition from square to round, creating a dynamic look that complements the floral forms. Arcata is available as a 1-light sconce and 6 or 8-light chandeliers with the choice between contemporary Gesso White or a luxurious Vintage Gold Leaf finish.

FINISHES

VINTAGE GOLD LEAF

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 15"

Width/Diameter: 39.5"

Minimum Height: 21.75"

Maximum Height: 63.75"

Canopy/Backplate: 5.5"

Hanging Type: 1-6" / 2-12" / 1-18" Stems

Product Weight: 23.1lb

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: No

Shade

ELECTRICAL



Bulb 1

Bulb Included: No

Socket: E12 Candelabra Base

Bulb Type: G16.5

Max Wattage: 10

Bulb Quantity: 6

Bulb Included: No

Wire Length: 144"

Cord Type: B & W TEFLON W/ GROUND WIRE

Gem Box Required (2"x3"): No

Dark Sky: No

SHIPPING

Carton 1: 44" x 40" x 14"

Carton 1 Weight: 37lb

Shipping Method: Truck Only

Country of Origin: PH

