



Project / Job Name: _____

Location: _____

Fixture Type: _____

Notes: _____

62-1800R1 - 7 Inch LED Disk Light; 27K/3K/35K/4K/5K CCT Selectable; White Finish; 6 Unit Contractor Pack



GENERAL

Company	NUVO
EA Height	8.27
EA Width	7.52
EA Length	9.09
Bulb Included	Integrated
Diameter	7.4
Dimmable Text	Forward Phase
Material	Steel
Fixture Type	Disk Light
Status	Active
Style	Contemporary
Surge Protection	Built-in surge protection - 2KV
CCT Selectable	Yes
Wattage Selectable	No
Finish Family	White
Amps	0.092A
Has Camera	No
IOT Enabled	No
Lens Finish	White
Lens Material	Polycarbonate (PC)
Lensed	Yes
Sloped Ceiling Compatible	Yes
Indoor Outdoor	Indoor
Product Technology	LED
Incandescent Equivalent	60W

ELECTRICAL

CCT (Kelvin Temp)	2700K/3000K/3500K/4000K/5000K
Dimmable	Yes-Dimmable
Hours Rated	50000
Beam Angle (degree)	110
Color Temp	Warm White to Natural Light
CRI	90+
Dimming Type	120V only, Phase cut
Operating Frequency	60Hz
Operating Temp	-20C (-4F) to +40C (+104F)
Lumens	930L
Volts	120v
Watts	11W

PHYSICAL

Lamp Base	Integrated
Finish	WHITE
ANSI Base	Integrated
Lamp Type	Integrated LED
Fixture Shape	Round

ADDITIONAL INFO

Warranty	5-Years
----------	---------

PACKAGING

UPC	045923406249
Case Cube	1.5566
Case Height	9.25
Case Length	18.7
Case Quantity	4
Case UPC	10045923406246
Case Weight	19.36
Case Width	15.55
EA Cube	0.3271
EA Height	8.27
EA Length	9.09
EA Quantity	1
EA Weight	4.41
EA Width	7.52
Pack Type	Contractor Box
Web Height	1.44
Web Width	7.4

COMPLIANCE

CA Prop 65	Lead
Energy Star ID	4520470
FCC Compliant	Yes
Location Rating	Wet
ROHS Compliant	Yes
Safety Listing	cETLus
California Ban	Lawful for sale
Energy Star Certified	Yes
Title 20	Exempt
T24 Compliant	Yes