



msi

MONITOR

Optix MAG241C



SPECIFICATION

DCI-P3 / sRGB	90% / Up to 115%
Panel Size	23.6"
Aspect ratio	16:9
Panel Resolution	1920 x 1080
Pixel Pitch (H x V)	0.27156(H) x 0.27156 (V)
Refresh Rate	144Hz
Response time	1ms (MPRT)
Viewing angle	178°
Curved	1500R
Brightness	300
Contrast Ratio	3000:1
Control	5-way OSD navigation joystick
Dimension (W x H x D)	536.4 x 411.5 x 225.24 mm
Weight	4.2kg / 6.4kg
DCR	100000000:1
Active Display Area (mm)	521.3952(H) x 293.2848(V)
Surface Treatment	Anti-glare
Display Colors	16.7M
Video ports	2 x HDMI(1.4)
USB ports	2 x USB 2.0 1 x USB 2.0 Type B (PC to Monitor)
Audio ports	1 x Earphone out
Kensington Lock	Yes
VESA Mounting	100 x 100 mm
Power Type	Internal Adaptor
Power Input	100~240V, 50~60Hz
Signal Frequency	55.3 to 162KHz(H) 48 to 144Hz(V)
Adjustment (Tilt)	Tilt: -5 ~ 20 Height : -
Adjustment (Height)	0 ~ 130 mm
Note	Display Port: 1920 x 1080 (Up to 144Hz) HDMI: 1920 x 1080 (Up to 144Hz)
Panel Type	VA

FEATURE



Curved Gaming

View more of your game with the 1800R curve rate that is perfect for gamers to play their games.



144Hz High Refresh Rate

Experience smooth gaming with a blazing fast 144Hz refresh rate, that gives you the upperhand in fast moving games.



1ms Fast Response Time

Eliminate screen tearing and choppy frame rates with 1ms response time.



Gaming OSD APP

Customize and set the ultimate monitor modes with keyboard & mouse in a very easy way.



Headset Hanger

Keep your headset in an easy to access space with the built-in headset hanger.



Frameless Design

With the narrow bezel, you will not even notice the monitor at all in the heat of the moment.



FreeSync technology

AMD FreeSync® will prevent screen tearing or stuttering, producing ultra-smooth and lag-free gameplay.



Anti-Flicker technology

MSI Anti-Flicker technology provides a very comfortable viewing experience by reducing the amount of screen flicker.

CONNECTIONS



- 1. 1x HDMI
- 2. 1x HDMI
- 3. 1x Display Port
- 4. 1x Headset
- 5. 2x USB 2.0 Type A
- 6. 1x USB 2.0 Type B
- 7. 1x Kensington Lock
- 8. Headset Hanger