



Technical Data

Color	Hi-Vis Yellow
Sizes Available	OS
Packaging	Bagged Each
Packed	144/Case
Case Dimensions (in)	21.26 x 20.08 x 15.75
Case Weight (lbs)	35.27
Country of Origin	China
Fabric	Mesh, Polyester
Closure	Elastic
Product Circularity	Reusable / Launderable

Care Instructions



Machine Wash



Water Temp 40°C



Do Not Bleach



Tumble Dry



Low Heat



25

PIP® EZ-Cool®

FR Treated Hi-Vis Hard Hat Visor and Neck Shade

- Extended visor at front to block sun from worker's eyes
- Drape at back to shade the neck
- Elastic at back for secure fit
- High visibility fabric and silver reflective tape
- Shields eyes and neck from the sun
- FR treated up to 25 washes
- Fits most cap style and full brim hard hats

KEY: Made from recycled or bio-based Launderable Recyclable via TerraCycle®

PIP GLOBAL SAFETY | PROTECTION EMPOWERED™

AMERICAS: +1 (800) 262-5755 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | www.pipglobalsafety.com

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED. 2026-07-22

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
396-801FR-YEL	Hi-Vis Yellow	OS	616314125201	01616314125200	02616314125209