ELA Q

LED Remote Fixtures

Intended Use
To be powered by Quantum® LED series unit or combo with high-output option as part of an emergency lighting system providing light for the path of egress. Remote lamp head matches the appearance of the Quantum LED series family units.

Features
- Single or twin heads available
- Fully adjustable lamp heads to meet all aiming requirements
- Indoor remotes are constructed of white, engineering grade thermoplastic that is impact- and scratch-resistant
- Outdoor remotes are standard grade cast aluminum, sealed and gasketed
- 12 parallel white LEDs per head
- The typical life of the LED lamp is 10 years
- Universal mounting base for use with single- or twin-head applications

Listings
UL Listed. Damp location listed (ELA Q) 50°F to 104°F (10°C to 40°C). Wet location listed (ELA QWP) 14°F to 122°F (-10°C to 50°C).



ELA Q

ELA QWP



ELA T Q



ELA T QWP

LED

ORDERING INFORMATION

Specifications subject to change.

Example: ELA Q L0304

Series	Housing		Number of heads		Fixture		Lamp Type		Options	
ELA	(blank)	White/gray[1]	(blank)	Single	Q	Quantum LED series adjustable lamp head	L0304	1.5W/3.6V LED lamps, per lamp head[2]	SD	For use with self-diagnostic fixtures[4]
	B	Black	T	Twin	QWP	Quantum LED series adjustable lamp head, weather-proof, cast aluminum	L0309	1.5W/9.6V LED lamps, per lamp head[3]		

ADDITIONAL INFORMATION

For additional product information, visit www.lithonia.com.

ACCESSORIES	
ORDER SEPARATELY	
ELA WG1	Wireguard, 15"W x 13-1/2" H x 6" D[5]

SPEFICATIONS	
Q SINGLE	6-5/8"W x 4-3/4"H
Q TWIN	8-1/4"W x 4-1/4"H
QWP SINGLE	4-1/2"W x 5-3/4"H
QWP TWIN	8-1/2"W x 5-3/4"H

Notes
1 White standard for Q, gray standard for QWP.
2 For use with ELM2 LED only.
3 For use with LHQM LED only.
4 SD must be ordered in combination with ELM2 LED and LHQM LED fixtures.
5 See spec sheet ELA WG.