



## G-Tek® 3GX®

Seamless Knit A3 Dyneema® Diamond Blended Glove with Polyurethane Coated Flat Grip on Palm & Fingers

- Seamless construction offers increased comfort and breathability
- Dyneema® Diamond & Nylon shell is lightweight and provides excellent dexterity, tactile sensitivity and cut resistance
- Polyurethane coatings take on the surface properties of the glove liner providing a tactile grip in dry and slightly oily conditions, ideal for applications that require dexterity for precise handling
- Knit Wrist helps prevent dirt and debris from entering the glove
- Color coded hems for easy size identification
- Washable, resistant to chemicals, water, and ultraviolet light
- ⚠️ **WARNING:** Cancer - [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)

## Applications

- Thin Coating, Good Grip for High Dexterity Handling
- Maintenance and Repair Operations
- Handling, Assembly and Sorting of Small to Medium Parts and Materials
- Shipping, Receiving and Packaging



## Technical Data

|                      |                                                   |
|----------------------|---------------------------------------------------|
| Color                | Gray                                              |
| Sizes Available      | XS-2XL                                            |
| Packaging            | Pair Bagged Retail Ready                          |
| Packed               | 6 Dozen/Case                                      |
| Case Dimensions (in) | 11.81 x 12.60 x 14.17                             |
| Case Weight (lbs)    | 13.23                                             |
| Country of Origin    | Viet Nam                                          |
| Liner Material       | Dyneema Diamond Technology                        |
| Coating              | Polyurethane                                      |
| Coating Color        | Gray                                              |
| Coating Coverage     | Palm & Fingers                                    |
| Grip                 | Flat                                              |
| Gauge                | 15                                                |
| Cuff                 | Knit Wrist                                        |
| Construction         | Coated Seamless Knit, Coreless Technology         |
| Product Circularity  | Reusable / Launderable<br>Recycled via Terracycle |

## Performance Data

|                     |       |
|---------------------|-------|
| Cut Level           | A3    |
| ANSI Abrasion Level | 6     |
| ANSI Puncture Level | 4     |
| EN 388              | 4X43C |

## Care Instructions



KEY: Made from recycled or bio-based Launderable Recyclable via TerraCycle®

**PIP GLOBAL SAFETY | PROTECTION EMPOWERED™**

AMERICAS: +1 (800) 262-5755 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | [www.pipglobalsafety.com](http://www.pipglobalsafety.com)

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED. 2026-07-28

## SKU Information

| SKU         | COLOR | SIZE | UPC          | UPC (INNER)    | UPC (CASE)     |
|-------------|-------|------|--------------|----------------|----------------|
| 19-D327/XS  | Gray  | XS   | 616314167751 | 01616314167750 | 02616314167759 |
| 19-D327/S   | Gray  | S    | 616314167737 | 01616314167736 | 02616314167735 |
| 19-D327/M   | Gray  | M    | 616314167720 | 01616314167729 | 02616314167728 |
| 19-D327/L   | Gray  | L    | 616314167713 | 01616314167712 | 02616314167711 |
| 19-D327/XL  | Gray  | XL   | 616314167744 | 01616314167743 | 02616314167742 |
| 19-D327/XXL | Gray  | 2XL  | 616314167768 | 01616314167767 | 02616314167766 |