



Project / Job Name:

Location:

Fixture Type:

Notes:

**S14349** - 6.5 Watt LED A19; 4000K CCT; Medium Base; Plastic; 120 Volt; 4-Pack



#### GENERAL

|                           |                                   |
|---------------------------|-----------------------------------|
| Company                   | SATCO                             |
| EA Height                 | 4.92                              |
| EA Width                  | 2.4                               |
| EA Length                 | 6.85                              |
| Material                  | Plastic                           |
| Fixture Type              | Miniature                         |
| Status                    | Active                            |
| Surge Protection          | Built-in-surge protection - 0.5KV |
| Total Harmonic Distortion | <150%                             |
| CCT Selectable            | No                                |
| Wattage Selectable        | No                                |
| Finish Family             | White                             |
| Amps                      | .065A                             |
| IOT Enabled               | No                                |
| Lens Finish               | Frosted                           |
| Lens Material             | Plastic                           |
| Lensed                    | Yes                               |
| Operating Position        | Universal                         |
| Power Factor              | >0.5                              |
| SDS Class                 | LED_Lamp                          |
| Indoor Outdoor            | Indoor and Outdoor                |
| Product Technology        | LED                               |
| Incandescent Equivalent   | 40W                               |

#### ELECTRICAL

|                     |                             |
|---------------------|-----------------------------|
| CCT (Kelvin Temp)   | 4000K                       |
| Dimmable            | Non-Dimmable                |
| Hours Rated         | 15000                       |
| Beam Angle (degree) | 230                         |
| Color Temp          | Cool White                  |
| CRI                 | 90+                         |
| Operating Frequency | 60Hz                        |
| Operating Temp      | -4F to +104F (-20C to +40C) |
| Lumens              | 450L                        |
| Volts               | 120v                        |
| Watts               | 6.5W                        |

#### PHYSICAL

|               |        |
|---------------|--------|
| Lamp Base     | Medium |
| Finish        | Frost  |
| Housing Color | White  |
| ANSI Base     | E26    |
| Lamp Type     | A19    |
| MOD Lamps     | 2.36   |
| MOL           | 4.09   |

#### ADDITIONAL INFO

|                            |         |
|----------------------------|---------|
| Warranty                   | 2-Years |
| Rated For Enclosed Fixture | Yes     |

#### FEATURES

|              |     |
|--------------|-----|
| Flicker Free | Yes |
|--------------|-----|

#### PACKAGING

|               |                |
|---------------|----------------|
| UPC           | 045923143496   |
| Case Cube     | 0.6996         |
| Case Height   | 10.39          |
| Case Length   | 14.49          |
| Case Quantity | 12             |
| Case UPC      | 10045923143493 |
| Case Weight   | 4.2            |
| Case Width    | 8.03           |
| EA Cube       | 0.0468         |
| EA Height     | 4.92           |
| EA Length     | 6.85           |
| EA Quantity   | 1              |
| EA Weight     | 0.3            |
| EA Width      | 2.4            |
| Pack Type     | Color Box      |
| Web Length    | 4.09           |
| Web Width     | 2.36           |

#### COMPLIANCE

|                   |                 |
|-------------------|-----------------|
| ADA Compliant     | No              |
| CA Prop 65        | Lead            |
| Dark Sky Rated    | No              |
| FCC Compliant     | Yes             |
| IP Rating         | IP20            |
| Location Rating   | Damp            |
| NSF Approved      | No              |
| ROHS Compliant    | Yes             |
| Safety Listing    | cETLus - Listed |
| California Ban    | Lawful for sale |
| Title 20          | Yes             |
| T24/JA8 Compliant | No              |