



|                        |               |                               |              |
|------------------------|---------------|-------------------------------|--------------|
| <b>EAN:</b>            | 4013288101334 | <b>Size:</b>                  | 105x55x14 mm |
| <b>Part number:</b>    | 05104612001   | <b>Weight:</b>                | 11 g         |
| <b>Article number:</b> | 848 HSS       | <b>Country of origin:</b>     | CN           |
|                        |               | <b>Customs tariff number:</b> | 82075060     |

- Twist bit for metal applications
- Hex shaft for very good power transfer
- HSS = high speed steel with split point
- Finely-tuned material elasticity for great durability
- Very good concentricity

High quality metal twist drill bits for precise drilling in metal. Made out of high speed steel (HSS). A finely-tuned material elasticity provides for a long service life. Very good concentricity. Tough viscous tempered bits ensure a particularly long service life. The hexagonal shaft ensures very good power transfer. Drive: ¼" hexagon, suitable for holders as per DIN ISO 1173-D 6.3.

**Web link**

<https://www.wera.de/en/05104612001>

Wera - 848 HSS

05104612001 - 4013288101334

Wera Werkzeuge GmbH

Korzter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: [info@wera.de](mailto:info@wera.de)




### Twist drill bits for metal applications



Twist drill bits - for metal applications

- 1/4" drive suitable for holders as per DIN 3126-D 6.3 (ISO 1173)
- Hexagon shaft for very high torque transfer
- HSS = high speed steel with cone point
- Finely adjusted material elasticity for long service life
- Excellent concentricity
- Tough-absorbing tempered bits for particularly long service life

#### Further versions in this product family:

|                    |  |  |  |
|--------------------|---|---|---|
|                    | mm  | mm  | mm  |
| 05104610001        | 3.0   | 16.00   | 38.0  |
| 05104611001        | 3.1   | 18.00   | 40.0  |
| <b>05104612001</b> | <b>3.3</b>  | <b>18.00</b>  | <b>40.0</b>   |
| 05104613001        | 4.0   | 20.00   | 44.0  |
| 05104614001        | 4.1   | 20.00   | 44.0  |
| 05104615001        | 4.2   | 20.00   | 45.0  |
| 05104616001        | 5.0   | 26.00   | 50.0  |
| 05104617001        | 5.1   | 26.00   | 50.0  |
| 05104618001        | 6.0   | 26.00   | 50.0  |
| 05104619001        | 6.8   | 30.00   | 50.0  |
| 05104620001        | 8.0   | 32.00   | 51.0  |
| 05104621001        | 8.5   | 33.00   | 53.0  |
| 05104622001        | 10.0  | 38.00   | 54.0  |

#### Web link

<https://www.wera.de/en/05104612001>

Wera - 848 HSS  
05104612001 - 4013288101334

Wera Werkzeuge GmbH  
Korzter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)