



Project / Job Name:

Location:

Fixture Type:

Notes:

S11669 - 40 Watt T8 LED; 96 Inch; 30K/35K/40K/50K/65K CCT Selectable; Fa8 Base; Type A+B; PET Coated; Non-Dimmable; 120-277 Volt



GENERAL

Company	SATCO
EA Height	1.06
EA Width	1.06
EA Length	94.21
Lamp Ballast Type AB	Type A/B
Lamp Filament	LED
Material	Glass / Plastic
Fixture Type	T8
Status	Active
Surge Protection	Built-in-surge protection - 0.5KV
Total Harmonic Distortion	<20%
CCT Selectable	Yes
Wattage Selectable	No
Finish Family	White
Amps	0.420-0.180A
Nominal Length	96.0
Operating Position	Universal
Power Factor	>0.9
SDS Class	LED_Lamp
Shatter Proof Type	PET Coated
Indoor Outdoor	Indoor
Product Technology	LED
Fluor Equiv	96W

ELECTRICAL

CCT (Kelvin Temp)	3000K/3500K/4000K/5000K/6500K
Dimmable	Non-Dimmable
Hours Rated	50000
Beam Angle (degree)	200
Color Temp	Soft White to Daylight
CRI	80+
Operating Frequency	50/60Hz
Operating Temp	-20C (-4F) to +45C (+113F)
Lumens	5500L
Volts	120V-277V
Watts	40W

PHYSICAL

Lamp Base	Single Pin
Finish	Frost
Housing Color	White
ANSI Base	Fa8
Lamp Type	T8
MOD Lamps	1.0
MOL	94.0

ADDITIONAL INFO

Warranty	5-Years
Rated For Enclosed Fixture	Yes

PACKAGING

UPC	045923116698
Case Cube	1.8151
Case Height	3.94
Case Length	96.26
Case Quantity	10
Case UPC	10045923116695
Case Weight	10.87
Case Width	8.27
EA Cube	0.061
EA Height	1.06
EA Length	94.21
EA Quantity	1
EA Weight	1.01
EA Width	1.06
Pack Type	Sleeve
Web Length	94.0
Web Width	1.0

COMPLIANCE

Dark Sky Rated	No
FCC Compliant	Yes
IP Rating	IP20
Location Rating	Damp
NSF Approved	Yes
ROHS Compliant	Yes
Safety Listing	cETLus - Listed
California Ban	Lawful for sale
Title 20	Exempt
T24 Compliant	No