



## Bouton® Optical Eva®

Rimless Safety Glasses with Gray / Pink Temple, Gray Lens and Anti-Scratch Coating

- Smaller and more narrow than standard safety glasses
- Eva's construction allows the eyewear to better fit the facial structure of a woman
- Provides a more secure fit on the nose
- Lightweight, rimless design provides all day user comfort
- Pink rubber co-molded temples provide a secure fit
- Molded nose bridge design to fit the vast majority of users
- 10 Base curve lens
- Meets ANSI Z87.1+
- Meets CSA Z94.3
- **WARNING:** Reproductive Harm - [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)

## Technical Data

|                      |                         |
|----------------------|-------------------------|
| Color                | Pink                    |
| Sizes Available      | OS                      |
| Packaging            | Bagged Each             |
| Packed               | 144 Pair/Case           |
| Case Dimensions (in) | 25.59 x 10.24 x 12.60   |
| Case Weight (lbs)    | 13.23                   |
| Country of Origin    | Malaysia                |
| Lens                 | Tinted                  |
| Frame Style          | Rimless                 |
| Lens Color           | Gray                    |
| Frame Fit            | Narrow Face             |
| Lens Coating         | Anti-Scratch            |
| Bridge               | Molded                  |
| Temple               | Rubber Tips             |
| Base Curve           | 10                      |
| Construction         | Womans Fit              |
| Certifications       | ANSI Z87.1              |
| Product Circularity  | Recycled via Terracycle |

## Applications

- Outdoor Work
- Construction Applications
- Public Works

KEY: Made from recycled or bio-based Launderable Recyclable via TerraCycle®

**PIP GLOBAL SAFETY | PROTECTION EMPOWERED™**

AMERICAS: +1 (800) 262-5755 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | [www.pipglobalsafety.com](http://www.pipglobalsafety.com)

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED. 2026-07-16

### SKU Information

| SKU          | FRAME COLOR | LENS   | LENS       |         | UPC          | UPC (INNER)    | UPC (CASE)     |
|--------------|-------------|--------|------------|---------|--------------|----------------|----------------|
|              |             |        | LENS COLOR | COATING |              |                |                |
| 250-10-0900  | Pink        | Clear  | Clear      | AS      | 616314055621 | 01616314055620 | 02616314055629 |
| 250-10-0904  | Pink        | Tinted | Pink       | AS      | 616314055645 | 01616314055644 | 02616314055643 |
| 250-10-0920  | Pink        | Clear  | Clear      | AS/AF   | 616314055638 | 01616314055637 | 02616314055636 |
| 250-10-5501  | Pink        | Tinted | Gray       | AS      | 616314056000 | 01616314056009 | 02616314056008 |
| 250-100-0018 | Brown       |        |            |         | 198987100315 | 10198987100312 | 20198987100319 |
| 250-100-0020 | Clear       |        |            |         | 198987100346 | 10198987100343 | 20198987100340 |
| 250-100-0021 | Smoke       |        |            |         | 198987100339 | 10198987100336 | 20198987100333 |
| 250-100-0029 | Amber       |        |            |         | 198987022747 | 10198987022744 | 20198987022741 |

KEY: AF = Anti-Fog / AR = Anti-Reflective / AS = Anti-Scratch / FL360 = Fogless 3Sixty / U = Uncoated