

SHENANDOAH

B8018-PBR

Drawing on the aesthetics of the Art Deco era, the Shenandoah scone marries fluted glass with contemporary industrial metalwork to create an updated, style-forward silhouette. Providing 360-degree illumination, a cylindrical shade is suspended from a robust Patina Brass arm, which is corrosion-resistant in all weather conditions. Available in two sizes, Shenandoah introduces a touch of elegance to outdoor spaces.

FINISHES

PATINA BRASS

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 18"

Width/Diameter: 4.75"

Canopy/Backplate: 4.75"

Product Weight: 3.7lb

Extension: 6"

Top to Center: 3.25"

Canopy/Backplate Shape: Rectangle

Sloped Ceiling Compatible: No

Living Finish: Yes

Uplight Only: Yes

Shade

Shade 1: Glass

Shade 1 Finish: Clear Optic

Shade 1 Top Width: 4"

Shade 1 Height: 8.75"

ELECTRICAL



Bulb 1

Bulb Included: No

Socket: E26 Medium Base

Bulb Type: T10-5.5

Max Wattage: 10

Bulb Quantity: 1

Bulb Included: No

Wire Length: 7"

Cord Type: B & W TEFLON W/ GROUND WIRE

Gem Box Required (2"x3"): No

Dark Sky: No

SHIPPING

Carton 1: 14" x 10" x 7"

Carton 1 Weight: 6lb

Shipping Method: Ground

Country of Origin: VN

