WESTGATE
THE FUTURE IS HERE...AND IT'S QUITE BRIGHT!

Beautiflex

JOB NAME: _____

DATE: _____

TYPE: _____



DIMENSIONS:

16.4'(L) x 0.47"(W)



ULR-IN-16F-HO-COB-WT

24V INDOOR COB RIBBON - WHITE TUNING

Ideal for undercabinet, soffit, display cases and toe kick lighting.

MODEL	WATTS PER FT.	VOLTAGE	LUMENS PER FT.	COLOR TEMP	REEL LENGTH	MAX RUN
ULR-IN-16F-HO-COB-WT	3W	24VDC	340LM	WT	16.4FT.	20FT

ELECTRICAL SPECIFICATIONS:

- Voltage: 24VDC (LED driver required)
- Wattage: 3W per ft.
- Max Run: 20ft.
- Efficacy: 113LM/W per ft.

HOUSING SPECIFICATIONS:

- Cutting increment: Every 1-1/8 inches
- 3M double sided tape (9474LE) is preinstalled
- Includes 1 female ribbon-to-power supply connector (Prewired) and 1 male plug for connection to next ribbon (Prewired)
- IP rating: IP20

CERTIFICATIONS: UL

UL LISTED

5 YEAR LIMITED WARRANTY

LIGHTING SPECIFICATIONS:

- LED Type: COB
- Total lumens: 340LM per ft.
- Color temperature: White Tuning (2700K to 6500K)
- Color rendering index: 90
- Beam Angle: 120°

WARRANTY: 5 years

Rev. 2022-09-30

WESTGATE
THE FUTURE IS HERE...AND IT'S QUITE BRIGHT!

Beautiflex

JOB NAME: _____

DATE: _____

TYPE: _____

ULR-IN-16F-HO-COB-WT


24V INDOOR COB RIBBON - HIGH OUTPUT

MODEL	WATTS PER FT.	VOLTAGE	LUMENS PER FT.	COLOR TEMP	REEL LENGTH	MAX RUN
ULR-IN-16F-HO-COB-WT	3W	24VDC	340LM	WT	16.4FT.	20FT

OPTIONAL ACCESSORIES:


MODEL	DESCRIPTION
ULR-M2-M3-3A	White-Tuning Ribbon Light Controller With Remote(190WMAX)
ULR-LTECH-E2	White-Tuning Ribbon Light Wall-Mount Controller
ULR-T86-JB	86 X 86 mm PVC Junction Box For Wall-Mount Controllers





ULR-LTECH-E2


- Input voltage: 24VDC
- Current Load: Max 4A
- Max Output power: 96W
- Wireless Frequency: RF 2.4GHz
- Working Temp: -22˚~131˚F
- Dimensions: 3.38" x 3.38" x 1.4"






ULR-T86-JB








ULR-M2-M3-3A

Remote Control

- Working voltage: 3V
- Working Frequency: 433MHz
- Remote Distance: 131~164 ft.
- Working Temp: -40˚~131˚F
- Dimensions: 4.1" x 2.36" x 0.35"

Receiving controller

- Input Voltage: 24VDC
- Max Output power: 216W
- Working Temp: -22˚~131˚F
- Dimensions: 5.3" x 1.18" x 0.79"



Required electronic driver

Rev. 2022-09-30