Fuse Outdoor | E30252-10BKGLD

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

Within a solid tube of Clear glass, a White cylindrical acrylic tube encases omnidirectional LED light. Its frame is constructed of aluminum finished in Matte Black and extends less than 4 inches from the wall for ADA compliance making this collection suitable for indoor and outdoor applications.



MEASUREMENTS

DIMENSION	: 18.5" W x 4.75" H x 4.25" Ext
BACK PLATE	: 18.5" W x 4.75" H x 2.25" HCO
HANGING WEIGHT	: 5.94 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 880 Rated (650 Del.)
BULB	: 1 x 12.5W LED DC Integrated , 12W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: 3-in-1: Triac, ELV, or 0-10V
CRI	: 90 CRI
COLOR_TEMP	: 3000K
LIGHTING_DIRECTION	: Omni

FINISHES OPTION

Black / Gold (BKGLD)

GLASS

Clear and White 10

MATERIAL

Stainless Steel, Glass

RATINGS

cETLus
Wet Location

ADDITIONAL

INSTALL UP/DOWN: Any
RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com