Dispatch | E24088-90NAB

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

Send a message on the wire. Two semi-spherical frosted glass domes are separated by a tube of LED light and suspended by Tobacco Brown leather straps. The frames are complete in a contrasting Natural Aged Brass finish making the contemporary design softer and more applicable to traditional settings.



*max overall height

MEASUREMENTS

DIMENSION	: 17.25" L x 11.75" W x 34" H
CANOPY	: 6.5" W x 1.5" H x 6.5" L
HANGING WEIGHT	: 13.7 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 1,260 Rated (750 Del.)
BULB	: 1 x 14W LED DC Integrated , 14W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: 3-in-1: Triac, ELV, or 0-10V
CRI	: 90 CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

Natural Aged Brass (NAB)

GLASS

Frosted 90

MATERIAL

Steel, Alumimium, Glass

RATINGS

cETLus
Dry Location

ADDITIONAL

SLOPE: 15
RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com