



P65

Technical Data



Color	Smoke
Sizes Available	OS
Packaging	Bagged Each
Packed	144 Pair/Case
Case Dimensions (in)	21.93 x 11.65 x 12.20
Case Weight (lbs)	10.80
Country of Origin	Taiwan
Lens	IR Filter
Frame Style	Full
Lens Color	Green
Frame Fit	Universal
Lens Coating	Anti-Scratch, Anti-Fog
Bridge	Molded
Temple	Spatula
Base Curve	6
Certifications	ANSI Z87.1, TAA Compliant

Bouton® Optical Traditional Spectacle

Full Frame Safety Glasses with Smoke Frame, IR Filter Shade 3.0 Lens and Anti-Scratch Coating

- Classic dual lens style with sturdy propionate frame
- Long lasting heavy-duty metal hinges
- Molded nose bridge design to fit the vast majority of users
- U-Fit® spatula temples with a wire core
- 6 Base curve lens
- Meets ANSI Z87.1+
- ⚠ **WARNING:** Reproductive Harm - www.P65Warnings.ca.gov

Applications

- Soldering
- Torch Blazing
- Cutting

SKU Information

SKU	FRAME COLOR	LENS	LENS COLOR	LENS	UPC	UPC (INNER)	UPC (CASE)
				COATING			
249-5907-207	Smoke	IR Filter	Green	AS/AF	616314102325	01616314102324	02616314102323
249-5907-400	Smoke	Clear	Clear	AS/AF	616314115479	01616314115478	02616314115477
249-5907-401	Smoke	Tinted	Gray	AS/AF	616314115486	01616314115485	02616314115484

KEY: AF = Anti-Fog / AR = Anti-Reflective / AS = Anti-Scratch / FL360 = Fogless 3Sixty / U = Uncoated