

Product data sheet

Characteristics

A150

Meter pak accy, hub, 1.50 in wire size, Series A, rainproof, 3.31 in



Main

Product or Component Type	Hub Conduit entry
Range of Product	Series A

Complementary

Cable entry	Conduit entry 1.5"
Device Composition	Adaptor plate
Hub type	A
Mounting Support	Direct mounting on box
Number of mounting holes	4
Product Certifications	UL Listed
Device Application	Conduit entry
Shape of screw head	Slotted hexagonal
Height	3 in (76.20 mm)
Width	3.3 in (83.82 mm)
Depth	3.3 in (83.82 mm)

Ordering and shipping details

Category	00039-METER SOCKETS & HUBS
Discount Schedule	DE4
GTIN	785901029502
Returnability	Yes
Country of origin	IN

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.30 in (8.38 cm)
Package 1 Width	3.30 in (8.38 cm)
Package 1 Length	1.00 in (2.54 cm)
Package 1 Weight	3.52 oz (99.79 g)
Unit Type of Package 2	CAR
Number of Units in Package 2	10
Package 2 Height	6.00 in (15.24 cm)
Package 2 Width	13.60 in (34.544 cm)
Package 2 Length	5.00 in (12.7 cm)
Package 2 Weight	2.70 lb(US) (1.225 kg)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Under investigation

Contractual warranty

Warranty	18 months
----------	-----------