

CLARISSE

H1132704-AGB/SAO

A classic lantern shape is reimagined with the spirit of modern romance. The hexagonal frame of Clarisse features arched glass panels that reveal cream candles. With a mix of Aged Brass and either Soft Bisque or Arctic Ocean finishes, each lantern is a festive celebration of color. Available as a small 3-light or large 4-light design.

FINISHES

AGED BRASS w/ SOFT ARCTIC BLUE

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 26.25"

Width/Diameter: 16"

Minimum Height: 29.5"

Maximum Height: 65.75"

Canopy/Backplate: 6"

Hanging Type: 54" Chain, 1-3" / 1-6" / 1-12" / 1-18"
Stems

Product Weight: 13lb

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: No

Shade

Shade 1: Glass

Shade 1 Finish: Clear

Shade 1 Top Width: 7.5"

Shade 1 Bottom L/W: 0" / 4"

Shade 1 Height: 17.25"

ELECTRICAL



Bulb 1

Bulb Included: No

Socket: E12 Candelabra Base

Bulb Type: G16.5

Max Wattage: 10

Bulb Quantity: 4

Wire Length: 120"

Cord Type: B & W TEFLON W/ GROUND WIRE

Gem Box Required (2"x3"): No

Dark Sky: No

SHIPPING

Carton 1: 19" x 19" x 23"

Carton 1 Weight: 19lb

Shipping Method: Ground

Country of Origin: VN

