



jalas® GRAN PREMIO 1870 OFF ROAD

ASTM F2413-18 M/I/C/SD 35/PR EN ISO 20345:2011 S2, SRC, HRO, CI

Learn more

Safety boot, toecap material aluminium, PU midsole, plastic shank, rubber outsole, upper material PU-coated leather

CHARACTERISTICS

- Highest level of protection
- Excellent grip
- Perfect fit
- Extra comfortable
- Excellent shock absorption

FUNCTIONS

- Wide fit
- Heat-resistant outsole
- Oil-resistant outsole
- Anti-static properties
- Bellows tongue
- Padded boot shaft
- Ventilating insole
- Pull loops
- Zipper
- Water repellent
- Double shock absorption zones
- Conforms with IEC 61340-5-1 (ESD)

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Toe injuries, Antistatic

PRIMARY ENVIRONMENTS OF USE

Outdoors, All-year use, Harsh environments

SPECIFICATION

TYPE Safety footwear, Boots/Ankle boots
CATEGORY Cat. II
FITTING Wide
COLLECTION Gran Premio
UPPER MATERIAL PU-coated leather
TOECAP MATERIAL Aluminium
LINING MATERIAL Technical fleece
INSOLE JALAS 8103 FX2 Pro-X
INNERSOLE MATERIAL Textile, Soft EVA, Polyester-based conductive thread, Double shock absorption zones in PORON® XRD®
MIDSOLE MATERIAL PU midsole
OUTSOLE MATERIAL Nitrile rubber outsole
FASTENING Laces, Zipper
SHOELACES LENGTH 160 cm
COLOUR Black
NET WEIGHT, (SIZE 42) 1.35 kg

COMPLIANCE

CE Cat. II

EAC TP TC 019:2011

ASTM F2413-18
M/I/C/SD 35/PR

EN ISO 20345:2011
S2, SRC, HRO, CI

FEATURES

- Anti-static properties
- Ergothan Shock Absorption System
- ESD
- Aluminium toecap
- Oil-resistant outsole
- Wide fit
- Heat-resistant outsole
- Water repellent
- Winter model
- Zipper

SIZE				ARTICLE NUMBER	EAN
EU	UK	US M	US W		
36	3	4	5	1870-36	6408487440847
37	4	5	6	1870-37	6408487440854
38	5	5.5	6.5	1870-38	6408487440861
39	6	6.5	7.5	1870-39	6408487440878
40	6.5	7.5	8.5	1870-40	6408487440885
41	7	8	9	1870-41	6408487440892
42	8	9	10	1870-42	6408487440908
43	9	9.5	11	1870-43	6408487440915
44	10	10.5	11.5	1870-44	6408487440922
45	10.5	11	12.5	1870-45	6408487440939
46	11	12	13	1870-46	6408487440946
47	12	13	14	1870-47	6408487440953
48	13	13.5	14.5	1870-48	6408487440960

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.