



Technical Data

Color	Clear
Sizes Available	OS
Packaging	Bagged Pair
Packed	200/Case
Case Dimensions (in)	23.00 x 14.50 x 20.50
Case Weight (lbs)	17.99
Country of Origin	China
Lens	Clear
Frame Style	Rimless
Lens Color	Clear
Lens Coating	, Anti-Scratch
Certifications	ANSI Z87.1, CSA Z94.3 Certified

UVEX® A700

Rimless Clear Frame, Clear Lens, Anti-Scratch Hardcoat

- Affordably priced for all of your work environments
- Aggressive styling provides a stylish fit for your everyday wearer
- Slim sizing fits small or narrow facial profile
- Lightweight design, flexible temples and soft temple tip pads provide a secure, wraparound fit and all-day comfort
- Molded universal nose bridge provides a comfortable fit
- All lenses provide 99.9% UV protection
- Meets ANSI Z87.1+
- Meets CSA Z94.3

SKU Information

SKU	FRAME COLOR	LENS	LENS COLOR	LENS COATING	UPC	UPC (INNER)	UPC (CASE)
A700	Clear	Clear	Clear	AS	040025108527	30040025108528	70040025108526
A700-EH	Clear				198987170196	10198987170193	20198987170190

KEY: AF = Anti-Fog / AR = Anti-Reflective / AS = Anti-Scratch / FL360 = Fogless 3Sixty / U = Uncoated